product data sheet

item no. 83.040.1252.0

IP switch WIENET UMS 4-C-2SC-FM

Unmanaged switch with 4 fast ethernet (10/100 Mbit/s), 2 Multimode SC ports, compact version



item no.	83.040.1252.0
EAN	4049088600951
order unit	1 piece(s)

certificates / approvals

c UL us LISTED

technical data

mounting method	DIN rail (top hat rail)
degree of protection (IP)	IP30
housing material	metal
manageable	no
ethernet	yes
power over Ethernet	no
Fast Ethernet	yes
Gigabit Ethernet	no
number of ports 10/100 Mbps RJ45	4
diagnostic LEDs	power/link status/data/data rate
10 gigabit Ethernet	no
number of ports 10/100/1000 Mbps RJ45	0
number of ports 100 Mbps SC	2
type of electric connection	screw connection
LED status indication	PWR1, PWR2, P-Fail; LNL/ACT
connector cross section	0.25mm²...2.5mm² (AWG26...AWG12)
wire strip length	8 mm

technical data

voltage type	DC
min. operating temperature	-10 °C
max. operation temperature	60 °C
storage temperature / transport min.	-40 °C
storage temperature / transport max.	85 °C
relative humidity min.	5 %
relative humidity max.	95 %
net weight	700 g

redundant power supply	2 power inputs

supply circuit

voltage type	DC
operating voltage min.	12 V
operating voltage max.	48 V
input current, max.	1.5 A
power consumption max.	< 6.5 W

dimensions

depth	95 mm
width	36.6 mm
height	140 mm
weight	700 g

technical drawing

