product data sheet

item no. 46.031.4456.7

connector RST16I3/2S B1 ZT3 S GN

RST® MINI connector, straight, number of poles 2, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, cable diameter 7.1 - 13 mm, color of coding/ contact carrier leaves green



item no.	46.031.4456.7
EAN	4049088579523
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	16 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	leaves green
Pole codification	1, 2
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	6002

connection data

cable diameter max.	13 mm
cable diameter min.	7.1 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.25 mm²
connection cross section fine stranded mm² max.	2.5 mm²
connection cross section fine stranded mm² min.	0.25 mm²
terminations per pole	1
sheath strip length	25 mm
wire strip length	8 mm

model

model	female
connection type	screw connection
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.132 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	74 mm
width	24 mm
height	24 mm

accessories

item no.	type	description
06.563.8653.1	cover for female connector SW	RST16i3/2 cover piece, for covering unused female connectors, color black
06.563.8753.1	cover for female connector SW	RST16i3/2 cover piece, for covering unused female connectors, with fastening belt, color black

assembly

item no.	type	description
46.030.1354.7	distributor RST16I2V 2R1 TGVG GN	RST® MINI distribution block 1I / 2O, rated voltage 250 V / 400 V, rated current 16 A, number of poles 2, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 2, pole codification 1, 2, mechanical coding yes, color of coding/ contact carrier leaves green, ral num
46.032.5056.7	device connector RST16I3/2S S1 M02 GN	RST® MINI device connector, standard, straight, M16, number of poles 2, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 16 A, color of coding/ contact carrier leaves green