product data sheet

item no. 46.423.5033.1

cable assembly RST16I2KSB- 25G 50BR03

RST® MINI connection cable, female - free end, number of poles 2, rated voltage 250 V / 400 V, rated current 16 A, cable type H07RN-F, total length 5 m, nominal cross section conductor 2.5 mm², color of coding/ contact carrier black



item no.	46.423.5033.1
EAN	4049088603303
order unit	10 piece(s)

certificates / approvals

technical data

note

note	The total length may vary up to + / - 3 %.

general

rated current	16 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	3
continuity resistor	34.95 mOhm
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	black
Pole codification	L, N
color of housing inclusive strain relief	black

model

type of construction	cable screw gland
connection type	screw connection
nominal cross section conductor	2.5 mm²
degree of protection (IP)	IP66/68 (3m;2h) /IP69
wire strip length	9 mm
sheath strip length	35 mm
preparation of conductor ends	ultrasonically compressed wire ends
cable type	H07RN-F
cable color	black
cable diameter min.	10.2 mm
cable diameter max.	11.7 mm
version of cable	female - free end

type of cord set	connection cable
version cable end 1	female
version cable end 2	free end
shielded	no


material

surface finish	silver-plated
halogen free	no
insulation components continous temperature	100 °C
fire load	4.932 kWh/St


dimensions

total length	5 m

technical drawing



N = blau/blue
L = braun/brown



Kodierung/coding C1
250V / schwarz/black

Bestell-Nr. order-no.	L	Beispiel exampel	Typ type
46.423.XX33.1	XX in dm-Schritten	46.423.1033.1 = 10dm/L = 1000mm	RST1612KSB- 25 10SW03

Weitere Daten siehe KATALOG oder eKATALOG. Additional data see CATALOG or eCATALOG.
www.wieland-electric.com eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: Sheet: 1 von of 1

Werkstoff / Material

Maßstab / Scale: 1:1

	Tag/Date	Name
gezeichnet drawn	05.03.2021	Duetsch T.

Elektronische Freigabe Electronic Release

Zeichnung Nr. / Drawing No.: T 46.423.0033.1 13K

Index

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

Index | Datum / Blatt Date / Sheet | Änderung / Revision

wieland

Type: RST1612

Bennenung/Title: KONFEKT. LEITUNG
Schraubanschluss ohne Drahtschutz
/screw-connection without wire protection

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit E gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.