product data sheet

item no. 4L.042.4043.9

device connector RST08i5/4S 21 M04H BL

RST® MICRO device connector, straight, number of poles 4, male, connection type screw connection, rated voltage 250 V / 400 V, rated current 8 A, longitudinal sealing yes, color of coding/ contact carrier light blue



item no.	4L.042.4043.9
EAN	4049088556623
order unit	50 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.positioning realised with flattened threadUse only one connector with contact sealing - either male or female connector.

general

rated current	8 A
rated voltage	250 V / 400 V
pollution degree	3
mechanical coding	yes
rated impulse voltage	2.5 kV
continuity resistor	0.55 mOhm
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	light blue
Pole codification	1, 2/N, 3, 4

connection data

connection cross section solid mm² max.	1 mm²
connection cross section solid mm² min.	0.2 mm²
connection cross section fine stranded mm² max.	1 mm²
connection cross section fine stranded mm² min.	0.22 mm²
terminations per pole	1
wire strip length	6 mm

model

model	male
connection type	screw connection
connecting thread metric	M16,6

angle of plug	straight
degree of protection (IP)	IP66/68 (3m;2h) /IP69
longitudinal sealed	yes
thickness of housings (electrical device)	5 mm

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0 kWh/St
surface finish	silver-plated

dimensions

length	23.9 mm
width	20 mm
height	20 mm

technical drawing

a Hinweis / note

gezeichnete Ausführung 41.042.4053.1
/drawn version 41.042.4053.1

Öffnungsmaßbild siehe 41.051.4053.1 14K
/opening dimension see 41.051.4053.1 14K









1 Bereich bedruckt für Kodierungsfarbe
/area printed for coding colour

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.


These dimensions will be especially checked at delivery
Only inspection dimensions
With E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit E gekennzeichnete Maße sind nur für interne Zwecke gültig


Weitere Daten siehe KATALOG oder eKatalog
additional data see CATALOG or eCATALOG
www.wieland-electric.com
eshop.wieland-electric.com

Teilenummer /part number	längsdicht /longitudinal sealing	Typ / type (b)	Kodierungsfarbe /color of coding	Kodierung /coding	Polkennzeichnung /pole marking
41.042.4053.1	nein / no	RST08i5/4S S1 M04H SW	tiefschwarz, RAL 9005 /jet black, RAL 9005		
4L.042.4053.1	ja / yes	RST08i5/4S 21 M04H SW			
41.042.4043.9	nein / no	RST08i5/4S S1 M04H BL	lichtblau, RAL 5012 /light blue, RAL5012		
4L.042.4043.9	ja / yes	RST08i5/4S 21 M04H BL			
41.042.4041.4	nein / no	RST08i5/4S S1 M04HL SG	schiefergrau, RAL 7015 /slate grey, RAL 7015		
4L.042.4041.4	ja / yes	RST08i5/4S 21 M04HL SG			
41.042.4041.8	nein / no	RST08i5/4S S1 M04HL KG	kieselgrau, RAL 7032 /pebble grey, RAL 7032		
4L.042.4041.8	ja / yes	RST08i5/4S 21 M04HL KG			





Auslieferungszustand
/delivery status



Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envolope principle. According to the envolope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance: DIN ISO 2768 - m

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: / First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Maßstab / Scale: 1:1

Werkstoff / Material

	Tag/Date	Name
gezeichnet / drawn	07.02.2020	Hollet

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: T 41.042.4053.1 13K b

Index

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

Index	Datum / Blatt Date / Sheet	Änderung / Revision
b	16.05.2024 /	
a	29.04.2022 /	

wieland

Type: RST08i5/4

Bennenung/Title: STECKERTEIL_GA
male connector

01-QU-RD-32/21