
product data sheet

item no. 92.050.9353.0

distributor GST18I5V 5P1 B V PB02



item no.	92.050.9353.0
EAN	4049088692000
order unit	20 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 2
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pastel blue
Pole codification	L, N, PE, D1, D2
RAL number coding/contact insert	5024

model

number of inputs	1
number of outputs	5
type of fastening	no
degree of protection (IP)	IP40
type of distributor	HH-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0 kWh/St
insulation components continous temperature	100 °C
surface finish	tin-plated

dimensions


length	59 mm
width	57.8 mm


height	64.4 mm


accessories

item no.	type	description
05.588.5753.0	lock GST18 VERTEILER WS	Locking device for distributer GST18i3-5, retrofit part, white
05.588.5753.1	lock GST18 VERTEILER SW	Locking device for distributer GST18i3-5, retrofit part, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9253.0	cover cap GST18I5 BUCHSEN	Cover for female connectors GST18i5, black

technical drawing







Bestellnummer order - no.	Farbe colour	Typ type
92.050.9353.0	pastellblau/ pastel blue	GST18i5 5P1 B V

Weitere Daten siehe KATALOG oder eKATALOG.
Additional data see CATALOG or eCATALOG.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1. Verwendung: First Use:

Blatt: 1 von 1
Sheet: 1 of 1

Werkstoff / Material

Maßstab / Scale: 1:1

	Tag/Date	Name
gezeichnet / drawn	27.06.2024	S. Schug

Elektronische Freigabe
Electronic Release

Zeichnung Nr. / Drawing No.: 92.050.9353.0 13K

Index: a

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

Index	Datum / Blatt Date / Sheet	Änderung / Revision
a	27.05.2025 /	

wieland

Type: GST18i5

Benennung/Title: Verteiler_HH_PB_K
/distributor

© Alle Rechte vorbehalten
© All rights reserved
Vertraulichkeitsklasse: Vertraulich
confidentiality class: confidential

These dimensions will be especially checked at delivery
Only inspection dimensions
With Ⓔ marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Ⓔ gekennzeichnete Maße sind nur für interne Zwecke gültig

2025-05-27 08:08:43 1.000

01-QU-RD-32/21