product data sheet

item no. 05.544.1929.8

male contact D 3,6- 2,5 QMM AG

Male contact, turned Ø 3,6 mm, 2,5 mm2, AWG 14, Ag



item no.	05.544.1929.8
EAN	4015573681736
order unit	100 piece(s)

certificates / approvals

technical data

general

wire strip length	10 mm
min. conductor cross section flexible wire	2.5 mm²
max. conductor cross section flexible wire	2.5 mm²
min. UL/CSA wire diamter flexible wire	14 AWG
max. UL/CSA wire diamter flexible wire	14 AWG
connection type	crimp
material	other
massive contact	yes
contact pin diameter	3.6 mm
inflammability class of insulation material acc. with UL94	other
contact resistance	≤ 1 mOhm