product data sheet

item no. 02.125.4629.7

female contact D 1,0- 0,09-0,25 QMM

Female contact, stamped Ø 1 mm, 0,09-0,25 mm2, AWG 28-24, Au



item no.	02.125.4629.7
EAN	4015573453982
order unit	100 piece(s)

certificates / approvals

technical data

general

wire strip length	3 mm
min. conductor cross section flexible wire	0.09 mm²
max. conductor cross section flexible wire	0.25 mm²
min. UL/CSA wire diamter flexible wire	28 AWG
max. UL/CSA wire diamter flexible wire	24 AWG
connection type	crimp
material	brass
massive contact	no
contact pin diameter	1 mm
inflammability class of insulation material acc. with UL94	other
contact resistance	≤ 5 mOhm