
product data sheet

item no. 75.015.5535.0

add-on housing FCS 4 7 SA BU SU

Surface-mounting housing podisCON 7-pole 20A; socket insert for podisCON plug; connecion round cable 4 mm² via screw terminal; degree of protection: IP65; with locking bracket; color: silver gray RAL 7001



item no.	75.015.5535.0
EAN	4015573840836
order unit	1 piece(s)

certificates / approvals

technical data

connection data

number of poles	7
number of clamp positions per pole	1
type of termination (round cable)	screw connection
type of connection power bus	plug-in connection

mechanical data

color housing	grey
degree of protection (IP)	IP65
mounting method	surface mounting

electrical data

rated voltage	500 V
rated current	20 A
type of supply voltage	AC/DC
rated operating voltage auxiliary power	250 V
rated operating current auxiliary power	20 A

dimensions

length	117 mm
assembly width	57 mm
assembly height	89 mm

accessories


item no.	type	description
06.502.5200.0	bit DIN 3128 PH1x70	Screwdriver bit PH1 x 70; Phillips size. 1; Shaft length 70 mm


assembly


item no.	type	description


75.015.0151.0	plug complete FCS 4 7 ST SA SO0	podisCON plug FCS 4.0 7 ST SA; 7-pole; pins; 20A, 500V, 4kV/3 (VDE); 600 V (UL, CSA); with M25 threaded joint for round cables 9-16 mm; screw connection 4.0 mm²; degree of connection: IP65; color: black
75.015.0151.2	plug complete FCS 4 7 ST SA SO2	podisCON plug FCS 4.0 7 ST SA; 7-pole; pins; 20A, 500V, 4kV/3 (VDE); 600 V (UL, CSA); with threaded connector M25 for threaded joint; screw connection

technical drawing









Bohrbild
drilling picture

frei von lackbenetzungsstörenden Substanzen
free from substances which inhibit adhesion

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit / Æ gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With / Æ marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167. (This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).	ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TQM-05/03 ist einzuhalten. Conformity with Wieland document UU-TQM-05/03 (list of prohibited / declarable hazardous substances) to be declared!
Freitoleranz nach General tolerance	CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed
1.Verwendung: First Use: -	Blatt: Sheet: 1 von of 1

Werkstoff/Material	2006	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
	gezeichnet drawn	08.02.	Schober	75.015.5535.0 01K	
Maßstab/Scale 1:1	geprüft checked	-	-		
	Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm	
Vol. mm³ Ofl./Surf. mm²	Ersatz für/Replacement for: -				

wieland
Elektrische Verbindungen

Type

Benennung/Title

RUNDLEITUNGS ABG
7-polig steckbar
circular cable waste 7 pole pluggable

Index	Datum / Blatt Date / Sheet	Änderung/Revision

QU-PEM-08/91