product data sheet

item no. 91.050.5953.0

distributor GST15I5Z 1P1 V WS

gesis® MINI intermediate coupling, without fastening option, number of poles 5, rated voltage 250 V / 400 V, rated current 16 A, number of inputs 1, number of outputs 1, color of coding/ contact carrier white



item no.	91.050.5953.0
EAN	4049088016516
order unit	100 piece(s)

certificates / approvals

technical data

general

rated current	16 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 1
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	3, N, PE, 2, 1
RAL number coding/contact insert	9016

model

number of inputs	1
number of outputs	1
type of fastening	no
degree of protection (IP)	IP20
type of distributor	intermediate coupling


material


housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.045 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions


length	32.4 mm
width	32 mm
height	12.5 mm


technical drawing






A-A






B-B



M/scale 1:1



Teilenummer/part no.	Farbe/color
91.050.5953.0	weiß/white
91.050.5953.1	schwarz/black

Toleranzierung nach DIN 7167/Tolerance system acc. to DIN 7167.
[This DIN-Standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances].

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TGM-05/03 ist einzuhalten. Conformity with Wieland document UU-TGM-05/03 [list of prohibited / declarable hazardous substances] to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material

Farbe/color: siehe Tabelle/see chart

Maßstab/Scale 2:1

Vol. mm³ Oft./Surf. mm²

	Tag/Date	Name
2008		
gezeichnet / drawn	01.06.	Winkler
geprüft / checked	-	-
Normgeprüft / Stand. check	-	-

Zeichnung Nr./Drawing No.: T 91.050.5953.0 01K Index: a

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Index	Datum / Blatt / Date / Sheet
a	03.06.2008/
Änderung/Revision	

wieland
Elektrische Verbindungen

Type

Benennung/Title

ZWISCHENKUPPLUNG

für/for GST1515

Netzanschluss/mains connection

OU-PEM-08/91

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With ℄ marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit ℄ gekennzeichnete Maße sind nur für interne Zwecke gültig

9105595300IK_4 CADM1025 Winkler 2008-06-03T10:43:08 1.000