product data sheet

item no. 96.052.4153.6

connector RST20I5S S1 ZR2SVA TB04

RST® CLASSIC connector, straight, number of poles 5, male, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier turquoise blue



item no.	96.052.4153.6
EAN	4015573877696
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	turquoise blue
Pole codification	L, N, PE, D1, D2
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	5018

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	4 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	4 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	4 mm²
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	male
connection type	screw connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.288 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	78.4 mm
width	34.6 mm
height	34.6 mm


accessories


item no.	type	description
05.565.9953.1	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, color black
99.532.0000.7	cover for male connector SW	RST20i5/4 cover piece, for covering unused male connectors, with fastening belt, color black

assembly

item no.	type	description
96.050.0153.6	distributor RST20I5B 3P1 F VGA TB04	RST® CLASSIC compact distributor 1I / 3O, rated voltage 250 V, rated current 20 A, number of poles 5, degree of protection (ip) IP66/68 (3m 2h) /IP69, number of inputs 1, number of outputs 3, pole codification L, N, PE, D1, D2, color of coding/ contact carrier turquoise blue, ral number codin
96.051.5053.6	device connector RST20I5S B1 M01 A TB0	RST® CLASSIC device connector, standard, straight, M25, number of poles 5, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue
96.453.1030.6	cable assembly RST20I5KSBS 25 10TB04	RST20i5 extension cable female - male, 5 pole, assembled with screw connection, application 250V with PE, 20A, cable type H07RN-F, length 1.0m, cross section 2.5mm², coding color turquoise blue
96.051.4153.6	connector RST20I5S B1 ZR2S A TB0	RST® CLASSIC connector, straight, number of poles 5, female, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier turquoise blue
96.051.6153.6	device connector RST20I5S B1 M03 A TB0	RST® CLASSIC device connector, modular, straight, M16, number of poles 5, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue
96.051.6053.6	device connector RST20I5S B1 M00 A TB0	RST® CLASSIC device connector, modular, straight, M20, number of poles 5, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue
96.053.6053.6	device connector RST20I5S B1 M90 A TB0	RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 5, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue
96.053.6253.6	device connector RST20I5S B1 M91 A TB0	RST® CLASSIC device connector, modular, angled 90°, M25, number of poles 5, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue
96.055.6153.6	device connector RST20I5S B1 M13 TB	RST® CLASSIC device connector, modular, angled 7°, M16, number of poles 5, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier turquoise blue

technical drawing






These dimensions will be especially checked at delivery
Only inspection dimensions
With -E marked dimensions are only valid for internal use


Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit -E gekennzeichnete Maße sind nur für interne Zwecke gültig

Auslieferungszustand
delivery status




Verpackungseinheit: je 100 Stück
packaging unit: per 100

A-A



Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. This document as well as the contents or parts of it are not to be passed on or reproduced, used or communicated for any purpose without express authorization. In the event of infringement of these rights, we will claim damages.



Type: RST2015S S1 ZR2SVA TB04 (a)

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167. (This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).						nein/no ☒	Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!
Freitoleranz nach General tolerance		CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed				1.Verwendung: First Use: -	Blatt: Sheet: 1 von of 1
/	/	Werkstoff/Material		2005	Tag/Date	Name	Zeichnung Nr./Drawing No. 96.052.4153.6 01K Index b
/	/			gezeichnet drawn	20.12.	Kneitz	
/	/	Maßstab/Scale 1:1		geprüft checked	-	-	
/	/			Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm
/	/	Vol. mm³	Oft./Surf. mm²	Ersatz für/Replacement for: -			
b	19.04.2012/	wieland Elektrische Verbindungen		Type	Benennung/Title STECKERTEIL_MIT_ZUGENTLASTUNG male connector with cord grip Schraubanschluss ohne Drahtschutz/screw-connection without wire protection Kodierung/keying A [250V/50V]		
a	06.02.2006/						
Index	Datum / Blatt Date / Sheet						
Änderung/Revision							

OU-PEM-08/91

9605241536301K_2 CADW2028 hoNet 2012-04-19T11:16:56 1.000