product data sheet

item no. 96.031.4153.9

connector RST20I3S B1 ZR2S BL0

RST® CLASSIC connector, straight, number of poles 3, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier light blue



item no.	96.031.4153.9
EAN	4015573981997
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	light blue
Pole codification	1, 2, 3
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	5012

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	6 mm²
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	female
connection type	screw connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.293 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	82 mm
width	34.6 mm
height	34.6 mm


accessories


item no.	type	description
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black
05.564.8653.1	manual disconnect RST20i3/i5 SCHWARZ	Manual disconnect for later installation of RST connectors, color black

assembly


item no.	type	description
96.032.5053.9	device connector RST20I3S S1 M01V BL0	RST® CLASSIC device connector, standard, straight, M25, number of poles 3, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
96.032.6153.9	device connector RST20I3S S1 M03V BL0	RST® CLASSIC device connector, modular, straight, M16, number of poles 3, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
96.032.6053.9	device connector RST20I3S S1 M00V BL0	RST® CLASSIC device connector, modular, straight, M20, number of poles 3, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
96.034.6053.9	device connector RST20I3S S1 M90V BL0	RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 3, model male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier light blue
96.036.6153.9	device connector RST20I3S B1 M13 BL07	RST20i3 device connector (7° angled) M16, 3 pole, male, screw connection, modular, application 250/400V, 20A, coding color light blue, color of housing black

technical drawing






Auslieferungszustand
delivery status



Verpackungseinheit: je 100 Stück
packing unit: per 100

A-A





Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Æ gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery
Only inspection dimensions
With Æ marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction of this document and utilization of the documents as well as the communication of its contents to others without express authorization is prohibited.

Toleranzierung nach DIN 7167/Tolerance system acc. to DIN 7167.
[This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances].

ja/yes ☒ Stoffverbots- und Deklarationsliste nach VU-TGM-05/03 ist einzuhalten. Conformity with Wieland document VU-TGM-05/03 [list of prohibited / declarable hazardous substances] to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: / First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material

Maßstab/Scale: 1:1

	Tag/Date	Name
2007		
gezeichnet / drawn	24.08.	Hallet
geprüft / checked	-	-
Normgep. Stand. check	-	-

Vol. mm³ Ofl./Surf. mm²

Zeichnung Nr./Drawing No.: T 96.031.4153.9 01K

Index

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

wieland
Elektrische Verbindungen

Type

Benennung/Title: BUCHSENTEIL_MIT_ZUGENTLASTUNG_

female connector with cord grip
Schraubanschluß ohne Drahtschutz/screw-connection without wire protection
Kodierung/keying 7 (250V/20A) Schaltanwendung/switching's application

Index | Datum / Blatt / Date / Sheet | Änderung/Revision

Teile-Nr./ part-nr.	Farbe:/ color:	Type
96.031.4153.9	lichtblau, ähnl.RAL 5012/ lightblue, similar to RAL 5012	RST2013S B1 ZR2S BL04

OU-PEM-08/91

9603141539101K_4 CADW1019 Morgen 2007-08-31T08:37:26 1.000