product data sheet

item no. 99.712.0000.7

cable assembly RST20I3K1BF 15 15SW

RST® CLASSIC mains connection cable, female - SchuKo plug, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H07RN-F, total length 1.5 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier black



item no.	99.712.0000.7
EAN	4015573983687
order unit	25 piece(s)

certificates / approvals

technical data

note

note	The total length may vary up to + / - 3 %.

general

rated current	16 A
rated voltage	250 V
rated impulse voltage	4 kV
continuity resistor	18.2 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
marking of poles	L, N, PE
color of housing inclusive strain relief	black

model

type of construction	shrinkage tube
connection type	crimp
nominal cross section conductor	1.5 mm²
degree of protection (IP)	IP20
wire strip length	9 mm
sheath strip length	35 mm
preparation of conductor ends	ultrasonically compressed wire ends
cable type	H07RN-F
cable color	black
cable diameter min.	9.5 mm
cable diameter max.	9.9 mm
version of cable	female - male CEE 7/4
type of cord set	mains connection cable
version cable end 1	female
version cable end 2	SchuKo plug

shielded	no

material

surface finish	silver-plated
halogen free	no
continuous temperature of cable	60 °C
insulation components continous temperature	100 °C
fire load	0 kWh/St

dimensions

total length	1.5 m