product data sheet

item no. 96.030.0153.1

distributor RST20I3V 3P1 F V SW

RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 3, rated voltage 250 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier black



item no.	96.030.0153.1
EAN	4015573735248
order unit	100 piece(s)

certificates / approvals

RINA

technical data

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
Pole codification	L, N, PE
RAL number coding/contact insert	9005

model

number of inputs	1
number of outputs	3
type of fastening	yes
degree of protection (IP)	IP66/68 (3m;2h) /IP69
type of distributor	distribution block

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.233 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions


length	55.5 mm
width	85.8 mm
height	31.3 mm


accessories


item no.	type	description
05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black

technical drawing


drawn construction:96.030.0153.0
Gezeichnete Ausführung: 96.030.0153.0








180°




packaging unit: per 100
Verpackungseinheit: je 100 Stk.

Teile-Nr.	Type	Farbe	Variante
96.030.0153.1	RST2013V_3P1_F_V__SW__	schwarz, ähnl. RAL 9005	mit Anschraubflansch
		black, similar to RAL 9005	with screwing flange
96.030.0153.0	RST2013V_3P1_F_V__GL__	grau, ähnl. RAL 7032	mit Anschraubflansch
		grey, similar to RAL 7032	with screwing flange
96.030.0253.1	RST2013V_3P1___V__SW__	schwarz, ähnl. RAL 9005	ohne Anschraubflansch
		black, similar to RAL 9005	without screwing flange
96.030.0253.0	RST2013V_3P1___V__GL__	grau, ähnl. RAL 7032	ohne Anschraubflansch
		grey, similar to RAL 7032	without screwing flange


scale 1:1
Maßstab 1:1






drawn construction: 96.030.0253.0
Ausführung: 96.030.0253.0

scale 1:1
Maßstab 1:1





drawn construction: 96.030.0153.0
Ausführung: 96.030.0153.0

Freitoleranz nach: -				CAD - Zeichnung, keine manuellen Änderungen				1.Verwendung: -		Nr.: 1 von 1
	/	Maßstab		-	2003	Tag	Name	Zeichnung Nr.		Index
	/	2:1			Entwurf	23.10.	Kneitz	T	96.030.0153.0 01K	c
	/				Gepruft	-	-			
c	30.04.2009/	Vol.	mm³	Gew.	mm³	Normgepr.	-	Ersatz für: -		
b	02.06.2006/	wieland						Benennung		
a	27.01.2006/							VERTEILER		
Aenderung	Datum / Blatt	Elektrische Verbindungen						DISTRIBUTION BLOCK		
Änderung								fuer RST2013/for RST2013		

Weitergabe sowie Vervielfältigung dieser Zeichnung, Verwertung und Mitteilung ihres Inhalts sind verboten, soweit nicht ausdrücklich zugestanden. All kinds of copying and reproduction of this drawing as well as the communication of its contents to others without express authorization are prohibited.

Diese Maße wurden bei Abteilung besonders geprüft
Bezeichnet mit ein Prüfmaß
Mit Z-Bohrmaschinen Maße sind nur für interne Zwecke gültig

96030015300 1K_4 CADAZ228 ho4d 2009-04-30 10:16:25 1:000