product data sheet

item no. 96.032.4153.1

connector RST20I3S S1 ZR2 V SW

RST® CLASSIC connector, straight, number of poles 3, male, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier black



item no.	96.032.4153.1
EAN	4015573769724
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
marking of poles	L, N, PE
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	9005

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	6 mm²
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	male
connection type	screw connection

degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.271 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	79.1 mm
width	34.6 mm
height	34.6 mm


accessories


item no.	type	description
05.564.4453.1	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, color black
99.416.6205.2	cover for male connector SW	RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black

assembly

item no.	type	description
96.030.0153.1	distributor RST20I3V 3P1 F V SW	RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 3, rated voltage 250 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier black
96.031.5053.1	device connector RST20I3S B1 M01 SW	RST® CLASSIC device connector, standard, straight, M25, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.031.4153.1	connector RST20I3S B1 ZR2 SW	RST® CLASSIC connector, straight, number of poles 3, female, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier black
96.031.6153.1	device connector RST20I3S B1 M03 SW	RST® CLASSIC device connector, modular, straight, M16, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.031.6053.1	device connector RST20I3S B1 M00 SW	RST® CLASSIC device connector, modular, straight, M20, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.033.6053.1	device connector RST20I3S B1 M90 SW	RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.035.6153.1	device connector RST20I3S B1 M13 SW	RST® CLASSIC device connector, modular, angled 7°, M16, number of poles 3, model female, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black

technical drawing







Schnitt A-A
section




Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.





M1:1



Verpackungseinheit: je 100 Stück
packaging unit: per 100

Teile-Nr./ part-nr.	Farbe:/ color:	Einz.-Tl.-Nr.: *)/ single-part-nr.:*)
96.032.4153.1	schwarz, ähnl. RAL 9005/ black, similar to RAL 9005	..._..._...._1
96.032.4153.0	lichtgrau, ähnl.RAL 7035/ lightgrey, similar to RAL 7035	..._..._...._0

Freitoleranz nach | CAD - Zeichnung, keine manuellen Änderungen | 1.Verwendung: - | Bl.: 1 von 1

Maßstab 1:1 | Werkstoff und Oberfläche: material and sureface: Farbe: siehe Tabelle color: look table | Vol. mm³ | Ofl. mm²

	Datum	Name
Entworfen	27.02.	Kneitz
Geprüft	-	-
Normgepr.	-	-

Buchstabe | Datum / Blatt | Änderung

wieland Elektrische Verbindungen

Type RST2013 S S1 ZR2 V

Benennung: STECKER_MIT_ZUGENTLASTUNG
male connector with cord grip
screw-connection without wire protection/Schraubanschluß ohne Drahtschutz

T | Zeichnung Nr. 96.032.4153.0 01K | Index a

Ersatz für: -

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit (Ø gekennzeichnete Maße sind nur für interne Zwecke gültig

9603241530O1K_4 04W007 Kneitz 2005-05-10T12:33:57 1.000