product data sheet

item no. 96.031.4153.1

connector RST20I3S B1 ZR2 SW

RST® CLASSIC connector, straight, number of poles 3, female, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier black



item no.	96.031.4153.1
EAN	4015573769649
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
Pole codification	L, N, PE
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	9005

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	6 mm²
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	female

connection type	screw connection
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.29 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	82 mm
width	34.6 mm
height	34.6 mm


accessories


item no.	type	description
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black


assembly

item no.	type	description
96.030.0153.1	distributor RST20I3V 3P1 F V SW	RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 3, rated voltage 250 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier black
96.032.5053.1	device connector RST20I3S S1 M01V SW	RST® CLASSIC device connector, standard, straight, M25, number of poles 3, model male, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.032.6153.1	device connector RST20I3S S1 M03V SW	RST® CLASSIC device connector, modular, straight, M16, number of poles 3, model male, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.032.6053.1	device connector RST20I3S S1 M00V SW	RST® CLASSIC device connector, modular, straight, M20, number of poles 3, model male, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.034.6053.1	device connector RST20I3S S1 M90V SW	RST® CLASSIC device connector, modular, angled 90°, M20, number of poles 3, model male, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black
96.036.6153.1	device connector RST20I3S S1 M13V SW	RST® CLASSIC device connector, modular, angled 7°, M16, number of poles 3, model male, connection type screw connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier black

technical drawing








Schnitt A-A
section A-A





Verpackungseinheit: je 100 Stück
packaging unit: per 100

Teile-Nr./ part-nr.	Farbe:/ color:	Einz.-Tl.-Nr.: *)/ single-part-nr.:*)
96.031.4153.1	schwarz, ähnl. RAL 9005/ black, similar to RAL 9005	..._..._...._1
96.031.4153.0	lichtgrau, ähnl.RAL 7035/ lightgrey, similar to RAL 7035	..._..._...._0

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. / Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1. Verwendung: / First Use:

Blatt: 1 von 1 / Sheet: 1 of 1

Maßstab / Scale: 1:1

Werkstoff / Material
Farbe: siehe Tabelle
colour: look table

	Tag/Date	Name
gezeichnet / drawn	27.02.2004	Kneitz
geprüft / checked		
Normgeor. Stand: check		

Zeichnung Nr. / Drawing No.: 96.031.4153.0 01K — Index: b

Maße in mm / Dimensions are in mm

Vol. mm³ Oft./Srf. mm²

Ersatz für / Replacement for:

Index	Datum / Blatt Date / Sheet	Änderung / Revision
b	04.05.2018 /	
a	03.05.2005 /	

wieland
www.wieland-electric.com

Type: RST2013 S B1 ZR2 V

Bennenung/Title: BUCHSENTEIL_MIT_ZUGENTLASTUNG
female connector with cord grip
Schraubanschluß o. Drahtschutz/screw connection without wire protection

Diese Maße werden bei Abnahme besonders geprüft / These dimensions will be especially checked at delivery
Ausschließlich Prüfmaße / Only inspection dimensions
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig / With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Lunz_96_031_4153_0_01K-AA-dwg1_main_2 CADW4035 Lunz 2018-05-04T11:01:37 1.000

QU-MEE-01/14 a