product data sheet

item no. 96.022.0350.8

# connector RST20I2F B23ZRYS B KG06

RST20i2 Connector, splitter connector, number of poles 2, male, connection type spring clamp connection, rated voltage 50 V / 120 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier pebble grey



| | |
|---|---|
| item no. | 96.022.0350.8 |
| EAN | 4049644011887 |
| order unit | 100 piece(s) |

## certificates / approvals

c UL us LISTED

## technical data

**note**

| | |
|---|---|
| note | fine stranded and stranded conductors require cable end sleeve |

**general**

| | |
|---|---|
| rated current | 20 A |
| rated voltage | 50 V / 120 V |
| rated impulse voltage | 4 kV |
| strain relief | yes |
| pollution degree | 3 |
| lockable | self-locking (unlocking by tool) |
| color of coding/ contact carrier | pebble grey |
| marking of poles | +, - |
| color of housing inclusive strain relief | black |

**connection data**

| | |
|---|---|
| cable diameter max. | 14 mm |
| cable diameter min. | 10 mm |
| connection cross section solid mm² max. | 2.5 mm² |
| connection cross section solid mm² min. | 0.5 mm² |
| connection cross section fine stranded mm² max. | 1.5 mm² |
| connection cross section fine stranded mm² min. | 0.5 mm² |
| terminations per pole | 2 |
| connection cross section stranded mm² min. | 0.75 mm² |
| connection cross section stranded mm² max. | 1.5 mm² |
| sheath strip length | 42 mm |
| wire strip length | 14.5 mm |

**model**

| | |
|---|---|
| model | male |
| connection type | spring clamp connection |
| degree of protection (IP) | IP66/68 (3m;2h) /IP69 |

**material**

| | |
|---|---|
| housing material | polyamide |
| halogen free | yes |
| contact material | CuZn |
| fire load | 0.496 kWh |
| insulation components continous temperature | 100 °C |
| surface finish | silver-plated |

**dimensions**

| | |
|---|---|
| length | 97 mm |
| width | 59 mm |
| height | 38 mm |

## accessories

| item no. | type | description |
|---|---|---|
| 05.564.4453.1 | cover for male connector SW | RST20i3/2 cover piece, for covering unused male connectors, color black |
| 99.416.6205.2 | cover for male connector SW | RST20i3/2 cover piece, for covering unused male connectors, with fastening belt, color black |
| 06.502.4300.0 | screwdriver DIN 5264 A 0,4 X 2,5 | Screw driver according to DIN 5264 A, blade: 0.4x2.5 mm, long and straight version |
| 95.101.1300.0 | ferrule crimping tool 0,08 - 10 mm² | Crimping tool for ferrules, wire strip length: 7-28 mm, nominal cross section: 0,08-10 mm², length of tool: 180 mm |
| 06.600.3627.0 | ferrule DIN 46228-E1-12 | RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.0 mm²/AWG17 |
| 06.600.3727.0 | ferrule DIN 46228-E0,75-12 | RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.75-1.0 mm²/AWG17 |
| 06.600.3827.0 | ferrule DIN 46228-E0,5-10 | RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.5 mm²/AWG20 |
| 06.600.3927.0 | ferrule DIN 46228-E1,5-12 | RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.5 mm²/AWG16 |

## assembly

| item no. | type | description |
|---|---|---|
| 96.020.0150.8 | distributor RST20I2V 3P1 F V L KG0 | RST20i2 Distributor, parallel connection, with fastening option, number of poles 2, rated voltage 50 V / 120 V, rated current 20 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier pebble grey |