Product data sheet

Item No. 96.222.7038.4

Cable assembly RST20I2K1-S315 L 70BR0

RST20i3/2 connection cable male - free end, 2 pole, assembled with shrinkage tube, application ~50V/-120V, 16A, cable type H07RN-F, length 7.0m, cross section 1.5mm², coding color signal brown



Item No.	96.222.7038.4
EAN	4015573946101
Order Unit	15 Piece(s)

Certificates / Approvals

Technical data

Note

Note	The total length may vary up to + / - 3 %.

General

Rated current	16 A
Rated voltage	50 V / 120 V
Rated impulse voltage	4 kV
Pollution degree	3
Lockable	self-locking (unlocking by tool)
Color of coding/ contact carrier	signal brown
Marking of poles	1, 2
Color of housing inclusive strain relief	black

Model

type of construction	Shrinkage tube
Connection type	Crimp
Nominal cross section conductor	1.5 mm²
Degree of protection (IP)	IP66/68 (3m;2h)
Wire strip length	9 mm
sheath strip length	35 mm
Preparation of conductor ends	ultrasonically compressed wire ends
Cable type	H07RN-F
Cable color	black
Cable diameter min.	8.5 mm
Cable diameter max.	9.7 mm
Version of cable	male - free end
Type of cord set	connection cable

Version cable end 1	free end
Version cable end 2	male
Shielded	No


Material


Surface finish	Silver-plated
halogen free	No
Continuous temperature of cable	60 °C
Insulation components continous temperature	100 °C
Fire load	0 kWh

Dimensions

Total length	7 m

Technical drawing





These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder GM-Eintragung vorbehalten. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-no.	L	Beispiel (Farbe: signalbraun) exampel (colour: signal brown)	Typ type
96.222.XX38.4	XX in dm-Schritten	96.222.1038.4 = 10dm/L= 1000mm	RST20I2K1-S315 L 10BR01
U6.222.XX38.4	XX in m-Schritten	U6.222.1238.4 = 12 m/L=12000mm	RST20I2K1-S315 LX12BR01

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material

Maßstab/Scale %

Vol. mm³ Oft./Surf. mm²

	Tag/Date	Name
2013		
gezeichnet drawn	18.07.	Schmitt J.
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No. T 96.222.0438.4 01K Index a

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: Zchng.v.14.11.2006 (a)

Index	Datum / Blatt Date / Sheet
a	18.07.2013/

Änderung/Revision

wieland
Elektrische Verbindungen

Type

Benennung/Title

KONFEKT_LEITUNG

freies Ende-Stecker Crimpausführung/free end-male pre-assembled cable crimp design K1 50V

96222043840K1K_2 CADW3029 Schmitt 2013-07-18T11:19:20 1.000

OU-PEM-08/91b