product data sheet

item no. 96.021.0353.1

connector RST20I2F B23ZRX SW

RST® CLASSIC connector, splitter connector, number of poles 2, female, connection type spring clamp connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier black



item no.	96.021.0353.1
EAN	4049644011559
order unit	100 piece(s)

certificates / approvals

c UL US LISTED

technical data

note

note	fine stranded and stranded conductors require cable end sleeve

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
marking of poles	L, N
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	9005

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.5 mm²
connection cross section fine stranded mm² max.	1.5 mm²
connection cross section fine stranded mm² min.	0.5 mm²
terminations per pole	2
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	1.5 mm²
sheath strip length	42 mm
wire strip length	14.5 mm

model

model	female
connection type	spring clamp connection
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.518 kWh/St
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	97 mm
width	59 mm
height	38 mm


accessories


item no.	type	description
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black
06.502.4300.0	screwdriver DIN 5264 A 0,4 X 2,5	Screw driver according to DIN 5264 A, blade: 0.4x2.5 mm, long and straight version
95.101.1300.0	ferrule crimping tool 0,08 - 10 mm²	Crimping tool for ferrules, wire strip length: 7-28 mm, nominal cross section: 0,08-10 mm², length of tool: 180 mm
06.600.3627.0	ferrule DIN 46228-E1-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.0 mm²/AWG17
06.600.3727.0	ferrule DIN 46228-E0,75-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.75-1.0 mm²/AWG17
06.600.3827.0	ferrule DIN 46228-E0,5-10	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 0.5 mm²/AWG20
06.600.3927.0	ferrule DIN 46228-E1,5-12	RST ferrule, for spring clamp contact, with insulating sleeve, for cross section 1.5 mm²/AWG16

assembly


item no.	type	description
96.020.0153.1	distributor RST20I2V 3P1 F V SW	RST® CLASSIC distributor, parallel connection, with fastening option, number of poles 2, rated voltage 250 V, rated current 10 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier black

technical drawing






Auslieferungszustand
delivery status



Verpackungseinheit: je 100 Stück
packaging unit: per 100

A-A





M 1:2

Weitere Daten siehe Katalog
further data see catalog

Teile-Nr. part-no.	Farbe colour	Type	
96.021.0353.1	schwarz/black RAL 9005	RST2012F B23ZRY	SW
96.021.0353.0	lichtgrau/light grey RAL 7035	RST2012F B23ZRY	GL

Toleranz nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach QU-TGM-05/03 ist einzuhalten. Conformity with Wieland document QU-TGM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach DIN ISO 2768 - m / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use:

Blatt/Sheet: 1 von/of 1

Werkstoff/Material

Maßstab/Scale: 1:1

Vol. mm³ Oft./Surf. mm²

Ersatz für/Replacement for: -

	Tag/Date	Name
2008 gezeichnet/drawn	04.11.	Dütsch T.
geprüft/checked	-	-
Normgeprüft/Stand. check	-	-

Zeichnung Nr./Drawing No.: T 96.021.0353.0 01K — Index

Maße in mm/Dimensions are in mm

Type

Benennung/Title: FEMALE CONNECTOR WITH DOUBLE CORD GRIP
BUCHSENTEIL_M_DOPPELZUGENTL
Federkraftanschluss / spring-clamp connection
Kodierung / coding 0 (250V/20A)

wieland
Elektrische Verbindungen

Index | Datum / Blatt / Date / Sheet
Änderung/Revision

OU-PEM-08/91

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With ℄ marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit ℄ gekennzeichnete Maße sind nur für interne Zwecke gültig

9602103530IK_4 C4DW1045 ausdsch 2008-11-04T09:21:53 1.000