product data sheet

item no. 96.023.4153.1

connector RST20I2S B13YR2 SW

RST20i3/2 connector (90° angled), 2 pole, female, screw connection, application 250V, 20A, for cable diameters 10-14mm, coding color black, color of housing black



item no.	96.023.4153.1
EAN	4049644011535
order unit	100 piece(s)

certificates / approvals

technical data

note

note	RST® terminals with screw clamping allow the connection of conductors without special preparation (without ferrules) according to EN 60999-1.

general

rated current	20 A
rated voltage	250 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	3
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
marking of poles	L, N
color of housing inclusive strain relief	black

connection data

cable diameter max.	14 mm
cable diameter min.	10 mm
connection cross section solid mm² max.	6 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	6 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	1
connection cross section stranded mm² min.	0.75 mm²
connection cross section stranded mm² max.	6 mm²
sheath strip length	26.5 mm
wire strip length	8 mm

model

model	female
connection type	screw connection
degree of protection (IP)	IP66/68 (3m;2h) /IP69

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0 kWh
insulation components continous temperature	100 °C
surface finish	silver-plated

dimensions

length	73.4 mm
width	34.6 mm
height	62.3 mm

accessories

item no.	type	description
99.414.6205.2	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, with fastening belt, color black
Z5.564.4553.1	cover for female connector SW	RST20i3/2 cover piece, for covering unused female connectors, color black

assembly

item no.	type	description
96.020.0153.1	distributor RST20I2V 3P1 F V SW	RST20i2 Distributor, parallel connection, with fastening option, number of poles 2, rated voltage 250 V, rated current 10 A, number of inputs 1, number of outputs 3, color of coding/ contact carrier black
96.022.4153.1	connector RST20I2S S13ZR2 V SW	RST20i2 Connector, straight, number of poles 2, male, connection type screw connection, rated voltage 250 V, rated current 20 A, cable diameter 10 - 14 mm, color of coding/ contact carrier black