product data sheet

item no. 93.430.2653.1

distributor BST14I3V 2P1T SW

gesis® NV T-distributor, without fastening option, number of poles 3, rated voltage 50 V, rated current 3 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier black



item no.	93.430.2653.1
EAN	4015573695597
order unit	100 piece(s)

certificates / approvals

technical data

general

rated current	3 A
rated voltage	50 V
rated impulse voltage	0.8 kV
pollution degree	2
mechanical coding	yes
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	black
marking of poles	1+, 2-
RAL-number coding/insert connector	9005

model

number of inputs	1
number of outputs	2
type of fastening	no
degree of protection (IP)	IP20
type of distributor	T-distributor


material

housing material	polyamide
halogen free	yes
contact material	other
fire load	0.034 kWh/St
insulation components continous temperature	100 °C
surface finish	gilt

dimensions

length	37 mm
width	13 mm
height	34 mm

technical drawing



Teile-Nr. part no.	Farbe colour	Typ type	
93.430.2653.0	weiß/white	BST1413V 2P1T	WS
93.430.2653.1	schwarz/black	BST1413V 2P1T	SW

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance: -

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: / First Use: -

Blatt: / Sheet: 1 von / of 1

Werkstoff/Material

Maßstab/Scale: 2:1

	2011	Tag/Date	Name
gezeichnet / drawn		04.01.	Dütsch T.
geprüft / checked		-	-
Normgepr. Stand. check		-	-

Zeichnung Nr./Drawing No.: T 93.430.2653.0 01K — Index

Maße in mm/Dimensions are in mm

Vol. mm³ Oft./Surf. mm²

Ersatz für/Replacement for: -

Änderung/Revision | Index | Datum / Blatt / Date / Sheet

wieland — Elektrische Verbindungen

Type

Benennung/Title: DISTRIBUTOR
VERTEILER
BST14.. steckbar/pluggable
Anwendung Standard / application standard

93_430_2653_0_01K_11-01-14_11h14m47s_Z CADW2037 Dütsch 2011-01-14T11:15:04 1.000

OU-PEM-08/91

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use
Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. All rights reserved. No unauthorized reproduction or use of this document or its contents or communication of its contents to others without express authorization is prohibited.