product data sheet

item no. 93.420.4653.0

distributor BST14I2V 2P1T PB02

gesis® NV T-distributor, without fastening option, number of poles 2, rated voltage 50 V, rated current 3 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier pastel blue



item no.	93.420.4653.0
EAN	4015573693883
order unit	100 piece(s)

certificates / approvals

technical data

general

rated current	3 A
rated voltage	50 V
rated impulse voltage	0.8 kV
pollution degree	2
mechanical coding	yes
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	pastel blue
marking of poles	1+, 2-
RAL-number coding/insert connector	5024

model

number of inputs	1
number of outputs	2
type of fastening	yes
degree of protection (IP)	IP20
type of distributor	T-distributor


material


housing material	polyamide
halogen free	yes
contact material	CuBe
fire load	0.034 kWh/St
insulation components continous temperature	100 °C
surface finish	gilt


dimensions


length	37 mm
width	13 mm
height	34 mm


technical drawing











M 1:1

Typ: BST1412V_2P1T_____PB02

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance: -

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: / First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material		2012	Tag/Date	Name	Zeichnung Nr./Drawing No. 93.420.4653.0 01K
		gezeichnet / drawn	16.04.	Ritter	Index
Maßstab/Scale 2:1		geprüft / checked	-	-	
		Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm

Vol. mm³ Oft./Surf. mm² Ersatz für/Replacement for: -

Index / Datum / Blatt / Date / Sheet — Änderung/Revision

wieland — Elektrische Verbindungen

Type

Benennung/Title

Verteiler

Distribution unit

BST14 Verteiler steckbar/BST14 Distribution unit pluggable

Dimmen/dim

OU-PEM-08/91

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Diese Maße werden bei Abnahme besonders geprüft / These dimensions will be especially checked at delivery

Ausschließlich Prüfmaße / Only inspection dimensions

Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig / With /E marked dimensions are only valid for internal use

9942046530 01K_2 CADM2031 Ritter 2012-04-16T11:01:12 1.000