product data sheet

item no. 93.421.0653.1

device connector BST14I2L B1 GN01

gesis® NV device connector, solder connector, horizontal, without fastening flange, number of poles 2, model female, connection type soldering connection, rated voltage 50 V, rated current 3 A, color of coding/ contact carrier green



item no.	93.421.0653.1
EAN	4015573600263
order unit	100 piece(s)

certificates / approvals

KEMA KEUR

technical data

general

rated current	3 A
rated voltage	50 V
pollution degree	2
mechanical coding	yes
rated impulse voltage	0.8 kV
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	green
marking of poles	1+, 2-
color of separate adapter (if present)	black

connection data

terminations per pole	1

model

model	female
connection type	soldering connection
angle of plug	square
degree of protection (IP)	IP20
built-in component	soldering connection

material

housing material	polyamide
halogen free	yes
contact material	CuBe
fire load	0.014 kWh/St
insulation components continous temperature	100 °C
surface finish	gilt

dimensions

length	26 mm
width	13 mm
height	11.75 mm

technical drawing

