product data sheet

item no. 93.420.0653.0

distributor BST14I2V 2P1T GN01

gesis® NV T-distributor, without fastening option, number of poles 2, rated voltage 50 V, rated current 3 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier green



item no.	93.420.0653.0
EAN	4015573695580
order unit	100 piece(s)

certificates / approvals

technical data

general

rated current	3 A
rated voltage	50 V
rated impulse voltage	0.8 kV
pollution degree	2
mechanical coding	yes
lockable	self-locking (unlocking by hand)
color of coding/ contact carrier	green
marking of poles	1+, 2-
RAL-number coding/insert connector	6017

model

number of inputs	1
number of outputs	2
type of fastening	no
degree of protection (IP)	IP20
type of distributor	T-distributor


material


housing material	polyamide
halogen free	yes
contact material	CuBe
fire load	0.035 kWh/St
insulation components continous temperature	100 °C
surface finish	gilt


dimensions


length	37 mm
width	13 mm
height	34 mm


technical drawing














M 1:1

Weitere Daten siehe Katalog
further data see catalog

Typ/type: BST1412V_2P1T_____GN01

Toleranzierung nach DIN 7167/Tolerance system acc. to DIN 7167.
[This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances].

ja/yes ☒ Stoffverbots- und Deklarationsliste nach VU-TGM-05/03 ist einzuhalten.
Conformity with Wieland document VU-TGM-05/03 [list of prohibited / declarable hazardous substances] to be declared!

Freitoleranz nach / General tolerance: -

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: / First Use: -

Blatt/Sheet: 1 von/of 1

Werkstoff/Material

Maßstab/Scale: 2:1

	Tag/Date	Name
2009		
gezeichnet / drawn	30.06.	Treschan
geprüft / checked	-	-
Normgeprüft / Stand. check	-	-

Zeichnung Nr./Drawing No.: 93.420.0653.0 01K

Index

Maße in mm/Dimensions are in mm

Vol. mm³ Oft./Surf. mm² Ersatz für/Replacement for: -

wieland
Elektrische Verbindungen

Type

Benennung/Title: VERTEILER
distributor

Index | Datum / Blatt / Date / Sheet | Änderung/Revision

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

OU-PEM-08/91

93420065300IK_4 G4DM2036 treschan 2009-06-30T11:28:22 1.000