product data sheet

item no. 92.944.3553.0

connector GST18I4S S1 ZR1 GR01

gesis® CLASSIC connector, number of poles 4, male, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 6.8 - 11.5 mm, color of coding/ contact carrier pebble grey



item no.	92.944.3553.0
EAN	4015573785632
order unit	50 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	2
mechanical coding	code 2
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pebble grey
marking of poles	2, N, PE, 1
color of housing inclusive strain relief	black
RAL-Nummer Codierung/Kontakteinsatz	7032

connection data

cable diameter max.	11.5 mm
cable diameter min.	6.8 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	2.5 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	2
sheath strip length	38.5 mm
wire strip length	7 mm

model

model	male
connection type	screw connection
degree of protection (IP)	IP40

material

housing material	polyamide
halogen free	yes

contact material	CuZn
fire load	0.123 kWh/St
insulation components continous temperature	100 °C
surface finish	tin-plated

dimensions

length	69.4 mm
width	38 mm
height	15 mm

accessories


item no.	type	description
05.587.3156.0	lock (G)ST18 WS	Locking device for cable to cable connection GST18i3-5, white
05.587.3156.1	lock (G)ST18 SW	Locking device for cable to cable connection GST18i3-5, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9153.0	cover cap GST18I4 BUCHSEN	Cover for female connectors GST18i4, black

assembly

item no.	type	description
92.943.3553.0	connector GST18I4S B1 ZR1 GR01	gesis® CLASSIC connector, number of poles 4, female, connection type screw connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 6.8 - 11.5 mm, color of coding/ contact carrier pebble grey
92.043.0058.0	device connector GST18I4L B1H WS	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 4, model female, connection type soldering connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier white
92.043.0158.0	device connector GST18I4L B1H GR01	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 4, model female, connection type soldering connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier pebble grey
92.207.1003.0	cable assembly GST18I4KSB- 15 10TR01	gesis® CLASSIC connection cable, female - free end, number of poles 4, rated voltage 250 V / 400 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier tomato red

technical drawing


Auslieferungszustand: unmontiert
delivery status: unmounted




Anwendung: Netzspannung
application: mains voltage

Teile-Nr. *part-no.*	Farbe *colour*	Typ *type*
92.944.3553.0	grau/ *grey*	GST18I4S S1 ZR1 GR01
92.944.3553.5	tomatenrot *tomato red*	GST18I4S S1 ZR1 TR01

Ansicht im montierten Zustand
drawn in assembled condition



M/scale 1:1



Toleranz Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size toleranzes).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance: DIN ISO 2768 - m

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use:

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material: 2015 | Tag/Date | Name

Farbe/colour: siehe Tabelle/ see table

gezeichnet/drawn: 23.1. Ritter K.

geprüft/checked: - -

Normgepr. Stand. check: - -

Maßstab/Scale: 2:1

Vol. mm³ Oft./Surf. mm²

Ersatz für/Replacement for: -

Zeichnung Nr./Drawing No.: 92.944.3553.0 01K

Index

Maße in mm/Dimensions are in mm

Type

Benennung/Title: *male connector with strain-relief*

STECKERTEIL_M_ZUGENTLASTUNG

Schraubanschluss/ screw connection

250/400V AC, 20A, 2,5qmm

wieland Elektrische Verbindungen

Index | Datum / Blatt Date / Sheet | Änderung/Revision

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery

Only inspection dimensions

Mit/Æ markierte Dimensionen sind nur für interne Zwecke gültig

Diese Maße werden bei Abnahme besonders geprüft

Ausschließlich Prüfmaße

Mit/Æ gekennzeichnete Maße sind nur für interne Zwecke gültig