product data sheet

item no. 92.033.0158.0

device connector GST18I3L B1H GR01

gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 3, model female, connection type soldering connection, rated voltage 250 V, rated current 20 A, color of coding/ contact carrier pebble grey



item no.	92.033.0158.0
EAN	4015573459199
order unit	100 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V
pollution degree	2
mechanical coding	code 2
rated impulse voltage	4 kV
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	pebble grey
Pole codification	L, N, PE

connection data

terminations per pole	1

model

model	female
connection type	soldering connection
angle of plug	square
inclination	90 °
degree of protection (IP)	IP20
built-in component	soldering connection

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.028 kWh/St
insulation components continous temperature	100 °C
surface finish	tin-plated

dimensions


length	24 mm
width	28.2 mm
height	13 mm

accessories


item no.	type	description
05.590.4556.0	lock GST18 WS	Locking device for solder connections GST18i3-5, white
05.590.4556.1	lock GST18 SW	Locking device for solder connections GST18i3-5, black
05.561.3653.0	cover cap GST18I3VS B WS	Cover piece for female GST18i3, white
05.561.3653.1	cover cap GST18I3VS B SW	Cover piece for female GST18i3, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.594.4250.0	cover cap ST18/3B + GST18I3 ST WS	
05.594.4253.0	cover cap ST18/3B + GST18I3 ST WS	


technical drawing


Schnitt A-A
cross section



Schnitt B-B
cross section







Weitere Daten siehe Katalog
further data see catalog

Teilenummer part number	Farbe colour	Typ type
92.033.0158.0	grau/grey	GST1813L B1H GR01
92.033.0158.5	tomatenrot brilliant red	GST1813L B1H TR01

Ⓐ

Toleranzierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance: -

CAD - Zeichnung, keine manuellen Änderungen. CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material: -

Maßstab/Scale: 2:1

Vol. - mm³ Oft./Surf. - mm²

Ersatz für/Replacement for: -

	Tag/Date	Name
gezeichnet drawn	12.05.	Schmitt J.
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 92.033.0158.0 01K Index b

Maße in mm/Dimensions are in mm

Index	Datum / Blatt Date / Sheet	Änderung/Revision
b	03.07.2013/	
a	06.05.2013/	

wieland
Elektrische Verbindungen

Type

Benennung/Title

BUCHSENTEIL Ⓑ

Lötanschl. rechtw./soldered connection horizontal
250V AC 20A

DU-PEM-08/91b

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use
Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

92033015B001K_2 CADWORK3D Lunz 2013-07-05T15:11:23 1.000