product data sheet

item no. 92.943.1053.0

connector GST18I4F B2 ZR2 WS

gesis® CLASSIC connector, number of poles 4, female, connection type spring clamp connection, rated voltage 250 V / 400 V, rated current 20 A, cable diameter 6.5 - 9 mm, color of coding/ contact carrier white



item no.	92.943.1053.0
EAN	4015573612860
order unit	50 piece(s)

certificates / approvals

technical data

general

rated current	20 A
rated voltage	250 V / 400 V
rated impulse voltage	4 kV
strain relief	yes
pollution degree	2
mechanical coding	code 1
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	2, N, PE, 1
color of housing inclusive strain relief	white
RAL-Nummer Codierung/Kontakteinsatz	9016

connection data

cable diameter max.	9 mm
cable diameter min.	6.5 mm
connection cross section solid mm² max.	2.5 mm²
connection cross section solid mm² min.	0.75 mm²
connection cross section fine stranded mm² max.	1.5 mm²
connection cross section fine stranded mm² min.	0.75 mm²
terminations per pole	2
sheath strip length	53 mm
wire strip length	9 mm

model

model	female
connection type	spring clamp connection
degree of protection (IP)	IP40
remark to type of connection	fine stranded and stranded conductors require cable end sleeve

material

housing material	polyamide

halogen free	yes
contact material	CuZn
fire load	0.158 kWh/St
insulation components continous temperature	100 °C
surface finish	tin-plated

dimensions

length	75 mm
width	42.25 mm
height	17 mm

accessories

item no.	type	description
05.587.3156.0	lock (G)ST18 WS	Locking device for cable to cable connection GST18i3-5, white
05.587.3156.1	lock (G)ST18 SW	Locking device for cable to cable connection GST18i3-5, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.566.9153.0	cover cap GST18I4 BUCHSEN	Cover for female connectors GST18i4, black

assembly

item no.	type	description
92.044.0058.0	device connector GST18I4L S1H WS	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 4, model male, connection type soldering connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier white
92.044.0158.0	device connector GST18I4L S1H GR01	gesis® CLASSIC device connector, solder connector, horizontal, without fastening flange, number of poles 4, model male, connection type soldering connection, rated voltage 250 V / 400 V, rated current 20 A, color of coding/ contact carrier pebble grey
92.207.1003.0	cable assembly GST18I4KSB- 15 10TR01	gesis® CLASSIC connection cable, female - free end, number of poles 4, rated voltage 250 V / 400 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier tomato red