product data sheet

item no. 91.020.1053.0

distributor GST15I2V 2P1T W WS

gesis® MINI T-distributor, without mounting option, cascadable, number of poles 2, rated voltage 250 V, rated current 16 A, number of inputs 1, number of outputs 2, color of coding/ contact carrier white



item no.	91.020.1053.0
EAN	4049088225307
order unit	100 piece(s)

certificates / approvals

technical data

general

rated current	16 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 1
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	white
Pole codification	L, N
RAL number coding/contact insert	9016

model

number of inputs	1
number of outputs	2
type of fastening	no
degree of protection (IP)	IP20
type of distributor	T-distributor

material

housing material	polyamide
halogen free	yes
contact material	CuZn
fire load	0.034 kWh/St
insulation components continous temperature	110 °C
surface finish	silver-plated

dimensions

length	34.4 mm
width	18.1 mm
height	29.5 mm

accessories

item no.	type	description
07.418.9153.1	supporting plate GST15 h-/H-VT	gesis®-Mounting plate for GST15 h- and H-distributors. for fastening to load-bearing, straight surfaces; fixing on cable trays with moulded expanding rivets; lying distributor mounting; color black

technical drawing

