product data sheet

item no. 99.800.4866.1

# flat cable outlet FCS 4 7 SI BU SW FM

podis® CON 7G4 flat cable outlet, with fix mounting plate, rated voltage 500 V, rated current 20 A, IP65, color housing black



| | |
|---|---|
| item no. | 99.800.4866.1 |
| EAN | 4049088077388 |
| order unit | 5 piece(s) |

## certificates / approvals

## technical data

**connection data**

| | |
|---|---|
| number of poles | 7 |
| number of clamp positions per pole | 1 |
| type of termination (round cable) | insulation piercing connection |
| type of connection power bus | plug-in connection |

**technical data UL/CSA**

| | |
|---|---|
| rated voltage | 600 V |
| rated current | 20 A |

**mechanical data**

| | |
|---|---|
| color housing | black |
| degree of protection (IP) | IP65 |
| mounting method | wire tray |

**electrical data**

| | |
|---|---|
| rated voltage | 500 V |
| rated current | 20 A |
| type of supply voltage | AC/DC |
| rated operating voltage auxiliary power | 250 V |
| rated operating current auxiliary power | 20 A |

**dimensions**

| | |
|---|---|
| length | 140 mm |
| assembly width | 60 mm |
| assembly height | 62 mm |

accessories

| item no. | type | description |
|---|---|---|
| 06.502.5200.0 | bit DIN 3128 PH1x70 | Screwdriver bit PH1 x 70; Phillips size. 1; Shaft length 70 mm |