product data sheet

item no. 73.100.4053.0

multipole adapter HD BAS WL 40 2,5 25

Multipole adapter revos HD 250V/10A 40 pole + ground, female insert, ground left



item no.	73.100.4053.0
EAN	4015573229228
order unit	4 piece(s)

certificates / approvals

technical data

general

model	female insert
size (in accordance with DIN 43880)	16
inflammability class of insulation material acc. with UL94	V2
color	grey
pollution degree	3
operating temperature range min.	-40 °C
operating temperature range max.	120 °C
suitable for modular version	no

connection data

connection type	screw connection
number of poles	40
plus switching contacts	0
number of pole for rated current 2	0
number of pole for rated current 3	0
total number of poles (without ground contact)	40
with wire protection	yes
Leiterquerschnitt starr (ein-/mehrdrähtig) Min.	0.5 mm²
Leiterquerschnitt starr (ein-/mehrdrähtig) Max.	2.5 mm²
protective contact	yes

technical data UL/CSA

nominal voltage according to UL/CSA	600 V
nominal current according CSA	10 A
min. conductor cross section flexible wire	0.5 mm²
max. conductor cross section flexible wire	2.5 mm²

conductor cross section flexible AWG wire	22-14 AWG

model

with housing	no
position of protective conductor	left

contacts

contact material	copper alloy
surface	tin-plated
wire strip length	12 mm
contact resistance	≤ 6 mOhm

screws head design/recomm. Torque

mounting screws	H1/0.5-0.7 Nm
clamping screws	M2.5/0.4-0.6 Nm Slot
ground conductor screws	H1/1.2-1.6 Nm

technical data DIN EN 61984


nominal voltage	250 V
nominal voltage face/ground	250 V
nominal current	10 A
rated impulse voltage	4 kV

assembly


item no.	type	description
76.326.4028.0	bottom BAS GUT GV 16H A	Bottom-base revos basic made of aluminum, with single locking lever forterminal adapters mounted on the rear, open, high version, 16-poles
76.327.4028.0	bottom BAS GUT GW 16H A	Bottom-base revos basic made of aluminum, with single locking lever andprotective cover for terminal adapters mounted on the rear, open, high version, 16-poles
73.326.4028.0	bottom BAS GUT GX 16H A	Bottom-base revos basic made of aluminum, with double locking lever forterminal adapters mounted on the rear, open, high version, 16-poles
73.327.4028.0	bottom BAS GUT GY 16H A	Bottom-base revos basic made of aluminum, with double locking lever andprotective cover for terminal adapters mounted on the rear, open, high version, 16-poles


technical drawing

Gezeichnete Ausführung
40-polig
Drawn version 40 poles



Ansicht ohne Abschlussplatte gezeichnet!
View is drawn without closing plate!





Weitere Daten siehe Katalog
further data see catalog

Teilenummer part number	Polzahl pole	A	B
73.100.4053.0	40	77,5	53,8
73.100.6453.0	64	104	84,3

Freitoleranz nach DIN -
CAD - Zeichnung, keine manuellen Änderungen
1.Verwendung: -
Bl.: 1 von 1

Maßstab 1:1
Werkstoff und Oberfläche:
2005 Tag Name
Entworfen 22.02. Schmitt J.
Geprüft - -
Normgepr. - -
Ersatz für: -
T Zeichnung Nr. 73.100.4053.0 01K Index

wieland
Elektrische Verbindungen

Benennung
KLEMMEN_ADAPTER
mit Buchseneinsatz, SL links
Terminal adaptor, socket insert earth left

Buchstabe Datum / Blatt
Änderung

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit (A gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction of this document and utilization of the document as well as the communication of its contents to others without express authorization is prohibited.