wieland

Product data sheet

Item No. 73.353.4045.1

Hood BAS GOE GA 16HM32 50 A1

Hood-EMV revos basic made of aluminum, for double locking lever or. screw cap with threaded hole M32 on the right side, low version, 16-poles

Item No.	73.353.4045.1
EAN	4015573844704
Order Unit	25 Piece(s)

Certificates / Approvals

Technical data

General

Housing material	aluminum
Color	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

Construction	16H
Model of the housing	male
Locking mechanism	Double locking levers
Cable entry	Sideways
Type of cable	Thread
With cable screw gland	No
Thread size M	32
Thread size PG	
Hinged lid	No
EMC-version	yes
Length	93.5 mm
Width	43 mm
Height	76 mm