product data sheet

item no. 73.345.6435.1

bottom BAS GUT GG 24HM32 50 A1

Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M32 on the left side, with protective cover, high version,24-polig



item no.	73.345.6435.1
EAN	4015573629950
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model

construction	24H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	sideways
type of cable	thread
with cable screw gland	no
thread size M	32
thread size PG	
hinged lid	yes
EMC-version	no
length	144 mm
width	57 mm
height	80 mm

technical drawing








Varianten/Variants
.0



73.34$^{5}_{1}$.6435.1	BAS GUT GG 24H M32/M25 A1	Gewindebohrung /Thread hole	X
73.34$^{5}_{1}$.6435.0	BAS GUT GG 24H M32/M25 A0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	dar-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog. **www.wieland-electric.com eshop.wieland-electric.com**

Bohrbild
/Cut out



Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance DIN ISO 2768 - m

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material: Aluminium beschichtet/ coated grau/ grey

Maßstab/Scale: 1:2

Vol. mm³ Ofl./Surf. mm²

	Name	Tag/Date
2014		
gezeichnet drawn	Treschan	25.08.
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 73.341.6435.0 13K

Index

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Index | Datum / Blatt Date / Sheet

Änderung/Revision

wieland
www.wieland-electric.com

Type: revos BASIC

Benennung/Title

GEHAEUSEUNTERTEIL

Baugröße 24H-Kabelabgang 1x M25/M32-links
housing size 24H-cable outlet 1x M25/M32-left

These dimensions will be especially checked at delivery / Only inspection dimensions

With Æ marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft / Ausschließlich Prüfmaße

Mit Æ gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.