product data sheet

item no. 73.358.6435.2

hood BAS GOT GD 24HM32 50 A2

Hood revos basic made of aluminum, with double locking lever and nozzleM32 on the right side, low version, 24-poles

item no.	73.358.6435.2
EAN	4015573627888
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model

construction	24H
model of the housing	male
locking mechanism	double locking levers
cable entry	sideways
type of cable	intermediate support
with cable screw gland	no
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	120 mm
width	57 mm
height	76 mm

technical drawing








Varianten/ Variants

.0 .2 .3 .4 .5



73.358.6435.5 (65/55)	BAS GOT GD 24H M40 M32 M25 A5	Kabelverschraubung(KV), IP65 /Cable gland(CG), IP65	
73.358.6435.4 (65/55)	BAS GOT GD 24H M40 M32 M25 A4	KV mit Zugentlastung, IP54 /CG with strain relief, IP54	
73.358/55.6435.3	BAS GOT GD 24H M32 M25 A3	KV mit Zugentlastung und Knickschutz, IP54 /CG with strain relief and bend support, IP54	
73.358.6435.2 (65/55)	BAS GOT GD 24H M40 M32 M25 A2	Zwischenstutzen /Bushing	
73.358.6435.1 (65/55)	BAS GOT GD 24H M40 M32 M25 A1	Gewindebohrung /Thread hole	X
73.358.6435.0 (65/55)	BAS GOT GD 24H M40 M32 M25 A0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	dar-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.

www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405 Ⓔ / Tolerance system Size ISO 14405 Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. (conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1. Verwendung: / First Use:

Blatt: 1 von 1 / Sheet: 1 of 1

Maßstab / Scale: 1:1

Werkstoff / Material: Aluminium beschichtet/ coated grau / grey

	Tag/Date	Name
gezeichnet / drawn	11.08.2014	TRESCHAN

Elektronische Freigabe / Electronic Release

Zeichnung Nr. / Drawing No.: T 73.355.6435.0 13K

Index: a

Maße in mm / Dimensions are in mm

Vol. mm³ Ofl./Srf. mm²

Ersatz für / Replacement for:

Index	Datum / Blatt / Date / Sheet
a	20.04.2021 /

Änderung / Revision

wieland

Type: revos BASIC

Bennenung/Title: GEHAEUSEOBERTEIL

Baugröße 24H-Kabelabgang 1x M25/M32/M40 seitlich
Hood size 24H-cable outlet 1xM25/M32/M40 side

Diese Maße werden bei Abnahme besonders geprüft / Ausschließlich Prüfmaße

Mit E gekennzeichnete Maße sind nur für interne Zwecke gültig

These dimensions will be especially checked at delivery / Only inspection dimensions

With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.