product data sheet

item no. 70.358.2435.1

hood BAS GOT GD 24 M32 A1

Hood revos basic made of aluminum, with double locking lever and threaded hole M32 on the right side, low version, 24-poles

item no.	70.358.2435.1
EAN	4015573651043
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24
model of the housing	male
locking mechanism	double locking levers
cable entry	sideways
type of cable	thread
with cable screw gland	no
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	120 mm
width	56 mm
height	70 mm

technical drawing





Varianten/ Variants

.0 .2 .3 .4 .5



70.35$^{8}_{5}$.2435.5	BAS GOT GD 24 M32 M25 A5	Kabelverschraubung(KV), IP65 /Cable gland(CG), IP65	
70.35$^{8}_{5}$.2435.4	BAS GOT GD 24 M32 M25 A4	KV mit Zugentlastung, IP54 /CG with strain relief, IP54	
70.35$^{8}_{5}$.2435.3	BAS GOT GD 24 M32 M25 A3	KV mit Zugentlastung und Knickschutz, IP54 /CG with strain relief and bend support, IP54	
70.35$^{8}_{5}$.2435.2	BAS GOT GD 24 M32 M25 A2	Zwischenstutzen /Bushing	
70.35$^{8}_{5}$.2435.1	BAS GOT GD 24 M32 M25 A1	Gewindebohrung /Thread hole	X
70.35$^{8}_{5}$.2435.0	BAS GOT GD 24 M32 M25 A0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	der-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material: Aluminium beschichtet/ coated grau/ grey

Maßstab/Scale: 1:2

Vol. mm³ Oft./Surf. mm²

	Tag/Date	Name
2013		
gezeichnet drawn	16.09.	Treschan
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 70.355.2435.0 13K

Index:

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Index | Datum / Blatt Date / Sheet

Änderung/Revision

wieland
Elektrische Verbindungen

Type: revos BASIC

Benennung/Title:

GEHAEUSEOBERTEIL

Baugröße 24-Kabelabgang seitlich-M25/M32
Hood size 24-cable outlet side-M25/M32

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Diese Maße werden bei Abnahme besonders geprüft / Ausschließlich Prüfmaße / Mit (E gekennzeichnete Maße sind nur für interne Zwecke gültig / These dimensions will be especially checked at delivery / Only inspection dimensions / With (E marked dimensions are only valid for internal use