product data sheet

item no. 73.347.4035.0

bottom BAS GUT GI 16HM32 50 A0

Bottom-base revos basic made of aluminum, with double locking lever andcable gland M32 on the bottom, with protective cover (IP54), low version, 16-polig

item no.	73.347.4035.0
EAN	4015573630000
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	below
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	yes
EMC-version	no
length	117 mm
width	57 mm
height	98 mm

technical drawing







Varianten/Variants
.0

73.347.1635.1 73.347.4035.1 73.343.4035.1	BAS GUT GI 16HM40 A1 BAS GUT GI 16HM32 A1 BAS GUT GI 16HM25 A1	Gewindebohrung /Thread hole	X
73.347.1635.0 73.347.4035.0 73.343.4035.0	BAS GUT GI 16HM40 A0 BAS GUT GI 16HM32 A0 BAS GUT GI 16HM25 A0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	dar-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog.
Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com

Bohrbild
/Cut out



Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ.
(This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten.
Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach DIN ISO 2768 - m
General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: -
First Use:

Blatt: 1 von 1
Sheet: of

Index	Datum / Blatt Date / Sheet	Änderung/Revision	Werkstoff/Material	2014	Tag/Date	Name	Zeichnung Nr./Drawing No. / Index
/	/		Aluminium	gezeichnet drawn	26.08.	Treschan	T 73.343.4035.0 13K
/	/	Maßstab/Scale 1:2	beschichtet/ coated	geprüft checked	-	-	
/	/		grau/ grey	Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm
/	/	Vol. mm³	Ofl./Surf. mm²	Ersatz für/Replacement for: -			

wieland
www.wieland-electric.com

Type: revos BASIC

Benennung/Title: GEHAEUSEUNTERTEIL
Größe/ housing size 16H-Kabelabgang/ cable outlet
2xM25 - 2xM32 - M32/M40 links/unten - left/down

These dimensions will be especially checked at delivery
Only inspection dimensions
With Æ marked dimensions are only valid for internal use
Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Æ gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster- oder Geschmacksmustereintragung vorbehalten. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.