product data sheet

item no. 73.340.4035.1

bottom BAS GUT GF 16HM25 50 A1

Bottom-base revos basic made of aluminum, for double locking lever withthreaded hole M25 on the left and right side, with protective cover, low version, 16-polig



item no.	73.340.4035.1
EAN	4015573629226
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP65
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model

construction	16H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	two-sided
type of cable	thread
with cable screw gland	no
thread size M	25
thread size PG	
hinged lid	yes
EMC-version	no
length	117 mm
width	57 mm
height	98 mm

technical drawing







Varianten/Variants


.0



73.34$^{4}_{0}$.4035.1	BAS GUT GF 16H M32/M25 A1	Gewindebohrung /Thread hole	X
73.34$^{4}_{0}$.4035.0	BAS GUT GF 16H M32/M25 A0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	dar-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog. **www.wieland-electric.com eshop.wieland-electric.com**

Bohrbild /Cut out



Toleranz Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance DIN ISO 2768 - m

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: - First Use:

Blatt: 1 von 1 Sheet: 1 of 1

Werkstoff/Material: Aluminium beschichtet/ coated grau/ grey

Maßstab/Scale: 1:2

Vol. mm³ Ofl./Surf. mm²

	Name	Tag/Date
2014 gezeichnet/drawn	Treschan	21.08.
geprüft/checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 73.340.4035.0 13K Index

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

Index / Datum / Blatt Date / Sheet

Änderung/Revision

wieland www.wieland-electric.com

Type: revos BASIC

Benennung/Title: GEHAEUSEUNTERTEIL

Baugröße 16H-Kabelabgang 2x M25/M32
housing size 16H-cable outlet 2x M25/M32

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use
Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung bleiben vorbehalten. Any reproduction, distribution or utilization of this document as well as the communication of its contents to others without express authorization is prohibited.