
product data sheet

item no. 73.337.4035.1

bottom BAS GUT GD 16HM32 50 A1

Bottom-base revos basic made of aluminum, with double locking lever or.screw cap with threaded hole M32 on the right side, low version, 16-polig



item no.	73.337.4035.1
EAN	4015573623385
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP65
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model

construction	16H
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	below
type of cable	thread
with cable screw gland	no
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	117 mm
width	57 mm
height	75 mm

technical drawing








Varianten/Variants
.0



73.33$^{7}_{3}$.4035.1	BAS GUT GD 16H $^{M32}_{M25}$ A1	Gewindebohrung /Thread hole	X
73.33$^{7}_{3}$.4035.0	BAS GUT GD 16H $^{M32}_{M25}$ A0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	dar-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog. **www.wieland-electric.com eshop.wieland-electric.com**



Bohrbild
/Cut out

Toleranz Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach WN 5020.010 ist einzuhalten. Conformity with Wieland document WN 5020.010 e (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance: DIN ISO 2768 - m

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Index	Datum / Blatt Date / Sheet	Änderung/Revision
/	/	
/	/	
/	/	
/	/	
/	/	
/	/	
/	/	

Maßstab/Scale: 1:2

Werkstoff/Material: Aluminium beschichtet/ coated grau/ grey

Vol. mm³ Ofl./Surf. mm²

	Tag/Date	Name
2014 gezeichnet/drawn	20.08.	Treschan
geprüft/checked	-	-
Normgepr. Stand. check	-	-

Ersatz für/Replacement for: -

Zeichnung Nr./Drawing No.: T 73.333.4035.0 13K

Index

Maße in mm/Dimensions are in mm

wieland
www.wieland-electric.com

Type: revos BASIC

Benennung/Title: GEHAEUSEUNTETEIL

Baugröße 16H-Kabelabgang 2xM25/M25-M32 links/unten
haus. size 16H-cable outl. 2xM25/M25-M32 left/down

Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig
Diese Maße werden bei Abnahme besonders geprüft / Ausschließlich Prüfmaße
These dimensions will be especially checked at delivery / Only inspection dimensions
With /E marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten. / The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.