product data sheet

item no. 70.340.1635.0

bottom BAS GUT GF 16 M25 A0

Bottom-base revos basic made of aluminum, for double locking lever withcable gland M25 on the left and right side, with protective cover (IP54), low version, 16-polig

item no.	70.340.1635.0
EAN	4015573618039
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16
model of the housing	surface mounting (base)
locking mechanism	double locking levers
cable entry	two-sided
type of cable	gland nut
with cable screw gland	yes
thread size M	25
thread size PG	
hinged lid	yes
EMC-version	no
length	117 mm
width	57 mm
height	57 mm

technical drawing







Varianten/Variants
.0

70.340.1635.1	BAS GUT GF 16 M25 A1	Gewindebohrung /Thread hole	X
70.340.1635.0	BAS GUT GF 16 M25 A0	Kabelverschraubung(KV),IP54 montiert /Cable gland(CG),IP54 assembled	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	der-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com



Bohrbild
/Cut out

Toleranzierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material		2013	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
Aluminium beschichtet/coated grau/grey	gezeichnet drawn	22.05.	Treschan	T	70.340.1635.0 13K	
Maßstab/Scale 1:2	geprüft checked	-	-			
	Normgepr. Stand. check	-	-		Maße in mm/Dimensions are in mm	
Vol. mm³	Oft./Surf. mm²	Ersatz für/Replacement for: -				

wieland
Elektrische Verbindungen

Type: revos BASIC

Benennung/Title: GEHAEUSEUNTERTEIL
Baugröße 16-Kabelabgang 2x M25
Housing size 16-Cable outlet 2x M25

Index | Datum / Blatt Date / Sheet | Änderung/Revision

Mit -K gekennzeichnete Maße sind nur für interne Zwecke gültig
Diese Maße werden bei Abnahme besonders geprüft Ausschließlich Prüfmaße
These dimensions will be especially checked at delivery Only inspection dimensions
With -K marked dimensions are only valid for internal use

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

70340163501K_2 CADW3028 Treschan 2013-09-20T12:46:08 1:000

OU-PEM-08/91b