product data sheet

item no. 72.250.1635.2

hood POW GOT GA 16 M40 69 A2

Hood revos basic made of aluminum, for double locking lever or. screw cap with nozzle M40 on the right side, low version, 16-poles



item no.	72.250.1635.2
EAN	4015573625679
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16XL
model of the housing	male
locking mechanism	double locking levers
cable entry	sideways
type of cable	intermediate support
with cable screw gland	no
thread size M	40
thread size PG	
hinged lid	no
EMC-version	no
length	94 mm
width	65 mm
height	95 mm