product data sheet

item no. 76.333.4035.0

# bottom BAS GUT GO 40HM25 50 A0

Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the bottom (IP54), low version, 40-polig



| | |
|---|---|
| item no. | 76.333.4035.0 |
| EAN | 4015573623989 |
| order unit | 1 piece(s) |

## certificates / approvals

## technical data

**general**

| | |
|---|---|
| housing material | aluminum |
| color | grey |
| surface | with powder coating |
| degree of protection (IP) | IP54 |
| UV resistant | yes |
| inflammability class of insulation material acc. with UL94 | other |
| operating temperature range min. | -40 °C |
| operating temperature range max. | 120 °C |

**model**

| | |
|---|---|
| construction | 16H |
| model of the housing | surface mounting (base) |
| locking mechanism | single locking lever |
| cable entry | below |
| type of cable | gland nut |
| with cable screw gland | yes |
| thread size M | 25 |
| thread size PG | |
| hinged lid | no |
| EMC-version | no |
| length | 117 mm |
| width | 57 mm |
| height | 80 mm |