product data sheet

item no. 76.330.4035.0

bottom BAS GUT GL 40HM25 50 A0

Bottom-base revos basic made of aluminum, with single locking lever andcable gland M25 on the right and left side (IP54), low version, 40-polig



item no.	76.330.4035.0
EAN	4015573623941
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	16H
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	two-sided
type of cable	gland nut
with cable screw gland	yes
thread size M	25
thread size PG	
hinged lid	no
EMC-version	no
length	117 mm
width	57 mm
height	80 mm