Product data sheet

Item No. 73.345.1035.1

Bottom BAS GUT GG 10HM32 50 A1

Bottom-base revos basic made of aluminum, with double locking lever andthreaded hole M32 on the left side, with protective cover, low version,10-polig



Item No.	73.345.1035.1
EAN	4015573844124
Order Unit	1 Piece(s)

Certificates / Approvals

Technical data

General

Housing material	aluminum
Color	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

Construction	10H
Model of the housing	Surface mounting (base)
Locking mechanism	Double locking levers
Cable entry	Sideways
Type of cable	Thread
With cable screw gland	No
Thread size M	32
Thread size PG	
Hinged lid	yes
EMC-version	No
Length	97 mm
Width	58 mm
Height	91 mm