product data sheet

item no. 73.354.1035.0

hood BAS GOT GC 10HM32 50 A0

Hood revos basic made of aluminum, for double locking lever or. screw cap with cable gland M32 on the top (IP54), low version, 10-poles



item no.	73.354.1035.0
EAN	4015573627284
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model


construction	10H
model of the housing	male
locking mechanism	double locking levers
cable entry	above
type of cable	gland nut
with cable screw gland	yes
thread size M	32
thread size PG	
hinged lid	no
EMC-version	no
length	73 mm
width	56 mm
height	70 mm

technical drawing





Varianten/ Variants



73.35$^{4}_{2}$.1035.5	BAS GOT GC 10H$^{M32}_{M25}$ A5	Kabelverschraubung(KV), IP65 /Cable gland(CG), IP65	
73.35$^{4}_{2}$.1035.4	BAS GOT GC 10H$^{M32}_{M25}$ A4	KV mit Zugentlastung, IP54 /CG with strain relief, IP54	
73.35$^{4}_{2}$.1035.3	BAS GOT GC 10H$^{M32}_{M25}$ A3	KV mit Zugentlastung und Knickschutz, IP54 /CG with strain relief and bend support, IP54	
73.35$^{4}_{2}$.1035.2	BAS GOT GC 10H$^{M32}_{M25}$ A2	Zwischenstutzen /Bushing	
73.35$^{4}_{2}$.1035.1	BAS GOT GC 10H$^{M32}_{M25}$ A1	Gewindebohrung /Thread hole	X
73.35$^{4}_{2}$.1035.0	BAS GOT GC 10H$^{M32}_{M25}$ A0	Kabelverschraubung(KV), IP54 /Cable gland(CG), IP54	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	dar-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog. **www.wieland-electric.com eshop.wieland-electric.com**

Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard describes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance: DIN ISO 2768 - m

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material	2014	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
Aluminium	gezeichnet drawn	16.06.	Treschan	T 73.352.1035.0 13K	
beschichtet/ coated	geprüft checked	-	-		
Maßstab/Scale 1:1	Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm	
grau/ grey					

Vol. mm³ Ofl./Surf. mm² Ersatz für/Replacement for: -

wieland www.wieland-electric.com

Type: revos BASIC

Benennung/Title: GEHAEUSEOBERTEIL

Baugröße 10H-Kabelabgang 1x M25/M32 von oben
hood size 10H-cable outlet 1x M25/M32 above

Index | Datum / Blatt Date / Sheet | Änderung/Revision

These dimensions will be especially checked at delivery
Only inspection dimensions
With Æ marked dimensions are only valid for internal use
Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit Æ gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder der Eintragung eines Gebrauchsmusters vorbehalten. Copying as well as the communication of its contents to others without express authorization is prohibited.