product data sheet

item no. 76.340.1035.1

bottom BAS GUT GR 10HM25 50 A1

Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M25 on the right and the left side, with protective cover, low version, 10-polig



item no.	76.340.1035.1
EAN	4015573844261
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	other
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	10
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	two-sided
type of cable	thread
with cable screw gland	no
thread size M	25
thread size PG	
hinged lid	yes
EMC-version	no
length	97 mm
width	58 mm
height	72 mm

technical drawing

