
product data sheet

item no. 71.333.1035.0

bottom BAS GUT GO 10 M20 A0

Bottom-base revos basic made of aluminum, with single locking lever andcable gland M20 on the bottom (IP54), low version, 10-polig



item no.	71.333.1035.0
EAN	4015573621862
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model

construction	10
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	below
type of cable	gland nut
with cable screw gland	yes
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	94 mm
width	52 mm
height	55 mm

technical drawing








Varianten/Variants
.0



71.33$^{7}_{3}$.1035.1	BAS GUT GO 10 M25 M20 A1	Gewindebohrung /Thread hole	X
71.33$^{7}_{3}$.1035.0	BAS GUT GO 10 M25 M20 A0	Kabelverschraubung(KV),IP54 montiert /Cable gland(CG),IP54 assembled	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	der gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com

Bohrbild
/Cut out



Toleranzierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen
CAD - drawing, no manual modifications allowed

1.Verwendung: - First Use:

Blatt: 1 Sheet: 1 von of 1

Werkstoff/Material	2013	Tag/Date	Name	Zeichnung Nr./Drawing No.	Index
Aluminium beschichtet/ coated grau/grey	gezeichnet drawn	25.06.	Treschan	T 71.333.1035.0 13K	
Maßstab/Scale 1:2	geprüft checked	-	-		
	Normgepr. Stand. check	-	-	Maße in mm/Dimensions are in mm	
Vol. mm³ Oft./Surf. mm²	Ersatz für/Replacement for: -				

wieland
Elektrische Verbindungen

Type: revos BASIC

Benennung/Title: GEHAEUSEUNTERTEIL
Baugröße 10-Kabelabgang 1xM20 unten
Housing size 10-cable outlet 1xM20 below

Index | Datum / Blatt Date / Sheet
Änderung/Revision

DU-PEM-08/91b

71333103501 3K_2 CADW3028 Treschan 2013-09-20T13:24:51 1:000