
product data sheet

item no. 70.333.0635.1

bottom BAS GUT GO 6 M20 A1

Bottom-base revos basic made of aluminum, with single locking lever andthreaded hole M20 on the bottom, low version, 6-polig



item no.	70.333.0635.1
EAN	4015573599598
order unit	1 piece(s)

certificates / approvals

technical data


general


housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP65
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C


model

construction	6
model of the housing	surface mounting (base)
locking mechanism	single locking lever
cable entry	below
type of cable	thread
with cable screw gland	no
thread size M	20
thread size PG	
hinged lid	no
EMC-version	no
length	84 mm
width	52 mm
height	54.7 mm

technical drawing








Varianten/Variants
.0



$70.33\frac{7}{3}.0635.1$	BAS GUT GO 6 M25/M20 A1	Gewindebohrung /Thread hole	X
$70.33\frac{7}{3}.0635.0$	BAS GUT GO 6 M25/M20 A0	Kabelverschraubung(KV), IP54 montiert /Cable gland(CG), IP54 assembled	
Bestellnummer /Order number	Typ /Type	Varianten /Variants	der-gestellt /drawed

Weitere Daten siehe KATALOG oder eKatalog. Additional data see CATALOG or eCatalog.
www.wieland-electric.com
eshop.wieland-electric.com

Bohrbild
/Cut out



Tolerierung Size ISO 14405Ⓔ/Tolerance system Size ISO 14405Ⓔ. (This ISO-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten. Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach General tolerance

CAD - Zeichnung, keine manuellen Änderungen CAD - drawing, no manual modifications allowed

1.Verwendung: First Use: -

Blatt: Sheet: 1 von of 1

Werkstoff/Material: Aluminium beschichtet/coated grau/grey

Maßstab/Scale: 1:2

Vol. mm³ Oft./Surf. mm²

	Tag/Date	Name
2013 gezeichnet drawn	03.05.	Treschan
geprüft checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 70.333.0635.0 13K

Index

Maße in mm/Dimensions are in mm

Ersatz für/Replacement for: -

wieland
Elektrische Verbindungen

Type: revos BASIC

Benennung/Title: GEHAEUSEUNTERTEIL

Baugröße 6-Kabelabgang 1x M20/M25 unten
Housing size 6-cable outlet 1x M20/M25 below

Index	Datum / Blatt Date / Sheet	Änderung/Revision

OU-PEM-08/91b

70333063501K_2 CADWORX28 Treschan 2013-09-20T11:26:56 1.000

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

Diese Maße werden bei Abnahme besonders geprüft / These dimensions will be especially checked at delivery
Ausschließlich Prüfmaße / Only inspection dimensions
Mit -K- gekennzeichnete Maße sind nur für interne Zwecke gültig / With -K- marked dimensions are only valid for internal use