product data sheet

item no. 92.232.1004.4

cable assembly GST18I3KS-S 15 10BR05

gesis® CLASSIC connection cable, male - free end, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 1 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier brown



item no.	92.232.1004.4
EAN	4049088236679
order unit	50 piece(s)

certificates / approvals

technical data

note

note	core colors with pole assignment: black (1), grey (2), brown (3)

general

rated current	16 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 4
continuity resistor	11.8 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	brown
Pole codification	1, 2, 3
color of housing inclusive strain relief	black

model

nominal cross section conductor	1.5 mm²
degree of protection (IP)	IP40
wire strip length	12 mm
sheath strip length	100 mm
preparation of conductor ends	ultrasonically compressed wire ends
cable type	H05VV-F
cable color	black
cable diameter max.	8.3 mm
version of cable	male - free end
type of cord set	connection cable
version cable end 1	free end

version cable end 2	GST18i3 plug

material

surface finish	tin-plated
halogen free	no
continuous temperature of cable	70 °C
insulation components continous temperature	100 °C
fire load	0.454 kWh/St
fire class	Eca


dimensions

total length	1 m

accessories


item no.	type	description
05.587.3156.0	lock (G)ST18 WS	Locking device for cable to cable connection GST18i3-5, white
05.587.3156.1	lock (G)ST18 SW	Locking device for cable to cable connection GST18i3-5, black
06.560.0300.0	mounting part GST18I3 SW	Lock system to provide accidental disconnection of "flying donnections" and to fix these connections to cable ladders or cable trays. Reduction of shearing forces on the strain reliefs Colour: black
06.561.7853.0	mounting frame GST18I3 SW	Mounting frame to snap in GST18i3 connectors into a housing or furniture. Wall thickness: 1,5-2,5 mm. Holds GST18i3 connectors with screw or spring connection and pre- assembled cables.
05.561.3653.0	cover cap GST18I3VS B WS	Cover piece for female GST18i3, white
05.561.3653.1	cover cap GST18I3VS B SW	Cover piece for female GST18i3, black
05.564.5353.0	cover cap GST18I3/4/5 SW	Cover piece 12 pole black for female parts GST18i3-6
05.564.5353.2	cover cap GST18I3/4/5 WS	Cover piece 12 pole white for female parts GST18i3-6
05.594.4250.0	cover cap ST18/3B + GST18I3 ST WS	
05.594.4253.0	cover cap ST18/3B + GST18I3 ST WS	


technical drawing



Ansicht in Pfeilrichtung "Y"
view in arrow direction "Y"

M 2:1





Teile-Nr. part-no.	L	Beispiel (Farbe: braun) example (colour: brown)	Typ type
92.232.XX04.4	XX in dm-Schritten	92.232.1004.4 = 10dm/L= 1000mm	GST1813KS-S 15 10BR05
U2.232.XX04.4	XX in m-Schritten	U2.232.1204.4 = 12 m/L=12000mm	GST1813KS-S 15 X12BR05

Tolerierung nach DIN 7167/Tolerance system acc. to DIN 7167.
(This DIN-standard desbribes the envelope principle. According to the envelope principle the deviations of form and parallelism are limited by the size tolerances).

ja/yes ☒ Stoffverbots- und Deklarationsliste nach UU-TOM-05/03 ist einzuhalten.
Conformity with Wieland document UU-TOM-05/03 (list of prohibited / declarable hazardous substances) to be declared!

Freitoleranz nach / General tolerance

CAD - Zeichnung, keine manuellen Änderungen / CAD - drawing, no manual modifications allowed

1.Verwendung: - / First Use: -

Blatt: 1 von 1 / Sheet: 1 of 1

Werkstoff/Material

Maßstab/Scale: x

2013

	Tag/Date	Name
gezeichnet / drawn	22.07.	Dütsch T.
geprüft / checked	-	-
Normgepr. Stand. check	-	-

Zeichnung Nr./Drawing No.: T 92.232.0204.4 01K

Index

Maße in mm/Dimensions are in mm

Vol. mm³ Oft./Surf. mm²

Ersatz für/Replacement for: -

Index / Datum / Blatt / Date / Sheet

Änderung/Revision

wieland
Elektrische Verbindungen

Type: GST1813 KS-S 15 ..BR05

Benennung/Title: KONFEKT_LEITUNG

Stecker-freies Ende Schraubausf./screw connection
250V AC 16A 1,5qmm

Weitere Daten siehe Katalog
further data see catalog

These dimensions will be especially checked at delivery
Only inspection dimensions
With /E marked dimensions are only valid for internal use

Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit /E gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.

DU-PEM-08/91b

92232020404K_2 CADW3027 Dvetsch 2013-07-24T08:14:20 1.000