product data sheet

item no. Z7.285.3027.0

insulated jumper bar IVB WKN 35 - 10

Cross connector, insulated for DIN rail terminal blocks type WKN ..., 10 -pole



item no.	Z7.285.3027.0
EAN	4015573158344
order unit	5 piece(s)

certificates / approvals

SEV-Ex


technical data

general

color	yellow
modular spacing	15.95 mm
number of bridged clamps	10
mounting method	screwable
insulated	yes
model	cross connector

technical drawing

3-polige Ausführung
3 poles variant



Diese Maße werden bei Abnahme besonders geprüft
Ausschließlich Prüfmaße
Mit (E gekennzeichnete Maße sind nur für interne Zwecke gültig

Teile-Nr. part nr.	Pol-zahl poles	L	l	Typ type
Z7.285.20MM.0	20	315,05	303,05	IVB WKN 35 M-20
Z7.285.22MM.0	2	27,95	15,95	IVB WKN 35-2
Z7.285.23MM.0	3	43,9	31,9	IVB WKN 35-3
Z7.285.24MM.0	4	59,85	47,85	IVB WKN 35-4
Z7.285.25MM.0	5	75,8	63,8	IVB WKN 35-5
Z7.285.26MM.0	6	91,75	79,75	IVB WKN 35-6
Z7.285.27MM.0	7	107,7	95,7	IVB WKN 35-7
Z7.285.28MM.0	8	123,65	111,65	IVB WKN 35-8
Z7.285.29MM.0	9	139,6	127,6	IVB WKN 35-9
Z7.285.30MM.0	10	155,55	143,55	IVB WKN 35-10
Z7.285.31MM.0	11	171,5	159,5	IVB WKN 35-11
Z7.285.32MM.0	12	187,45	175,45	IVB WKN 35-12

MM

27 Katalogteil
catalogue part

97 spezielle Verpackung
special packing

Freitoleranz nach DIN | CAD - Zeichnung, keine manuellen Änderungen | 1.Verwendung: - | Bl.: 1 von 1

Maßstab: /

	2002	Tag	Name
Entworfen		06.03.	Treschan
Geprüft		-	
Normgepr.		-	-

Zeichnung Nr.: T Z7.285.2027.0 01K | Index

Ersatz für:

wieland
Elektrische Verbindungen

Typ: IVB WKN 35-..

Benennung: VERBINDUNGSSTEG
jumper bar

Buchstabe	Datum / Blatt
Änderung	

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. In the event of the publication and distribution of this document as well as the communication of its contents to others without express authorization is prohibited.

Z7285202701 CAM.028 treschan 06.03.2002 14:36:23 1.000