
product data sheet

item no. 56.703.9953.0

installation terminal WKIF 2,5 N-D

Installation rail terminal blocks with tension spring connection for mounting on TS 35, nominal cross section: 2.5 mm², width: 5 mm, color: grey



item no.	56.703.9953.0
EAN	4049088037283
order unit	50 piece(s)

certificates / approvals

technical data

general

nominal cross section	2.5 mm²
basic color	grey
number of levels	2
number of clamp positions per level	2
width/grid dimension	5 mm
insulating housing	PA666
inflammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail) 35/7.5 mm
terminal blocks for electrical installations	yes

technical data

rated current	24 A
rated voltage	400 V
rated impulse voltage	4 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	95 mm

connection data

connection type 1	spring clamp connection
connection type 2	spring clamp connection
minimum cross section solid	0.14 mm²
maximum cross section solid	4 mm²
minimum cross section fine stranded	0.14 mm²
maximum cross section fine stranded	2.5 mm²

wire strip length	11 mm

technical data UL/CSA

cross section UL	22-12 AWG
current factory wiring	20 A
current field wiring	20 A
cross section CSA	22-14 AWG
voltage CSA	300 V
current CSA	20 A