product data sheet

item no. 55.504.9153.0

earth terminal WKM 4 SL / 15/V0

Ground terminal with Screw connection for mounting on TS 15 , nominal cross section: 4 mm², width: 6 mm, color: Green-yellow



item no.	55.504.9153.0
EAN	4015573210424
order unit	100 piece(s)

certificates / approvals

CAN-Ex KEMA EUR ATEX

technical data

general

nominal cross section	4 mm²
color	green/yellow
number of levels	1
number of clamp positions per level	2
width/grid dimension	6 mm
insulating housing	PA666
inflammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail) 15 mm
terminal blocks for electrical installations	yes
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail) 15 mm
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklemmen für Installationsverteiler	yes

technical data

rated impulse voltage	6 kV
pollution degree	3
closing plate required	yes
type of insulation material	thermoplastic
length	31.6 mm

connection data

connection type 1	screw connection
connection type 2	screw connection
minimum cross section solid	0.5 mm²
maximum cross section solid	6 mm²

minimum cross section fine stranded	0.5 mm²
maximum cross section fine stranded	4 mm²
wire strip length	9 mm
torque conductor mounting	0.5 Nm
torque rail mounting	0.5

technical data UL/CSA

cross section UL	22-14 AWG
voltage UL	300 V
current factory wiring	30 A
current field wiring	30 A
cross section CSA	22-10 AWG

accessories

item no.	type	description
98.090.0015.0	mounting rail TS 15 PERF - l:2000mm	Mounting rail TS 15, slotted, Höhe 5,5 mm, length 2 m, material steel. galv. zinc-plated and passivated
07.311.0753.0	end plate APM 4 SL / 15	End plate for DIN rail terminal blocks type WKM 4 SL..., color: grey
04.242.6053.0	marking tag strips 9705 A / 6 / 10	Marking tag strips for DIN rail terminal blocks type 9700 A / 6…, 10 tags per strip, color: white, unmarked, markable with Wieplot plotter- system

technical drawing

