product data sheet

item no. 76.326.6428.0

bottom BAS GUT GV 24H A

Bottom-base revos basic made of aluminum, with single locking lever forterminal adapters mounted on the rear, open, high version, 24-poles

item no.	76.326.6428.0
EAN	4015573230989
order unit	1 piece(s)

certificates / approvals

technical data

general

housing material	aluminum
color	grey
surface	with powder coating
degree of protection (IP)	IP54
UV resistant	yes
inflammability class of insulation material acc. with UL94	other
operating temperature range min.	-40 °C
operating temperature range max.	120 °C

model

construction	24H
model of the housing	equipment mounted (feed-through)
locking mechanism	single locking lever
cable entry	none
type of cable	none
with cable screw gland	no
thread size PG	
EMC-version	no
length	140 mm
width	43 mm
height	27.9 mm